





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
GW	-		A	-	05APR2001	BL



Recommended PCB-layout pitch 2.54.



- 5) All dimensions are maximum dimensions unless otherwise specified.
- 4) Mating face according to DIN 47295/CECC 22240.
- 3) Mounting hole of front panel : max $\varnothing 11.2$ if 1393679-3 is used.
- 2 Center conductor : excentric snap on PCB.
- 1 Nominal dimensions.



1:1

Cross reference table

Old part number	Tyco part number	Description	Material	Plating
V23612-A1227-A4	2-1393681-3	Outer conductor	Brass	1 μ m Au min in contact area
		Center conductor	CuBe	1 μ m Au min in contact area
		Dielectric	PEEK+PTFE	-

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN B. Lenvain CHK K. Mattheeuws APVD R. Leeman	08MAR2001 05APR2001 05APR2001	tyco Electronics Tyco Electronics Oostkamp - Belgium	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME Right angle PCB jack 75 ohm 1.6/5.6	
		0 PLC $\pm$ 1 PLC $\pm$ 2 PLC $\pm$ 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm$		SIZE A3	
MATERIAL -		FINISH -		CAGE CODE 00779	
				DRAWING NO C-2-1393681-3	
				RESTRICTED TO -	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1	
				REV A	