

# Summary Accessories

Backplane		Page
166873	Backplane with screw terminals to ADS_E 50/5 and ADS_E 50/10	260
133346	Backplane with screw terminals to choke on plug-in card 133350	
199950	Backplane with screw terminals to MIP 50-eurocard, 200629	273
245963	Backplane with screw terminals to MIP 100-eurocard, 246244	273

Front panel		Page
167850	Front panel 3HE / 5TE for ADS_E 50/5, clear anodised	260
168910	Front panel 3HE / 7TE for ADS_E 50/10, clear anodised	260
169356	19"-front panel 3HE / 21TE, suitable for PCU 1-axis controller, 169352	
169357	19"-front panel 3HE / 28TE, suitable for PCU 2-axis controller, 169353	
200640	19"-front panel 3HE / 8TE, suitable for MIP 50 / 100 Eurocard, 200629 / 246244	273

Motor choke		Page
133350	Choke on plug-in card, 4 x 0.5 mH, each 4.00 A, Eurocard format, incl. front panel 3HE / 8TE	260
137303	Choke module, 3 x 0.25 mH, each 5.00 A, L x W x H (90 x 70 x 49 mm) with screw terminals	259/260
232359	Choke module, 3 x 0.15 mH, each 10.00 A, L x W x H (90 x 70 x 49 mm) with screw terminals	259/260/268
107892	Motor choke block, 2 x 0.2 mH, each 4.00 A, L x W x H (32 x 32 x 20 mm) for print assembly	
107893	Motor choke block, 2 x 0.32 mH, each 3.15 A, L x W x H (32 x 32 x 20 mm) for print assembly	
107894	Motor choke block, 2 x 0.8 mH, each 3.15 A, L x W x H (43 x 43 x 25 mm) for print assembly	273

Power supply		Page
108153	Transformer primary: 230 VAC, secondary: 34 VAC / 4 A suitable for 169352, 169353	
108155	Transformer primary: 230 VAC, secondary: 34 VAC / 8 A suitable for 169352, 169353	

Cable		Page
275829	EPOS power cable (length 3 m) for 275512, 300583	
275851	EPOS motor cable (length 3 m) for 275512, 300583	
303490	EPOS motor cable (length 3 m) for 302287	
275878	EPOS Hall sensor cable (length 3 m) for 275512, 300583	
302948	EPOS motor / Hall sensor cable (length 3 m) for 302287	
275934	EPOS encoder cable (length 3 m) for 275512, 300583	
275932	EPOS signal cable (length 3 m) for 275512, 300583	
300586	EPOS signal cable 2 (length 3 m) for 300583	
275900	EPOS RS232-COM cable (length 3 m) for 275512, 300583	
275908	EPOS CAN-COM cable (length 3 m) for 275512, 300583	
275926	EPOS CAN-CAN cable (length 3 m) for 275512, 300583	
275937	EPOS CAN terminal resistance for 275512, 300583	
276248	EPOS connecteur set for 275512, 300583	
303807	EPOS connecteur set for 302287	
134796	PCU power cable (length 3 m) for 169352, 169353	
134797	PCU motor cable (length 3 m) for 169352, 169353	
133367	MIP & PCU, RS232-COM cable (length 3 m) for 169352, 169353, 108971	
134795	MIP & PCU, encoder cable (length 3 m) for 169352, 169353, 108971	
108088	MIP motor / power cable (length 3 m) for 108971	

Adapter		Page
108977	MIP test connecteur to 108971	
220300	Adapter flex print connector 11 poles on screw terminal 8 poles suitable for maxon flat motor	
220310	Adapter flex print connector 4 poles on screw terminal 4 poles suitable for maxon flat motor	
223774	Adapter spring contact strip according to DIN41651 10 poles on screw terminals 8 poles	267/268
262359	Adapter pin bar according to DIN41651 10 poles on screw terminals 10 poles	
232818	Adapter for MIP 10 / MIP 20 and encoder MR with Line Driver	
251590	Adapter for MIP 10 / MIP 20 and encoder MR without Line Driver	
246398	Adapter RS 232 / RS 485 for MIP Bus	
249634	Adapter for DEC 24/1: Flex print connector 8 poles, top contact style, pitch 0.5 mm	
249635	Adapter for DEC 24/1: Flex print connector 11 poles, top contact style, pitch 1.0 mm	
249636	Adapter for DEC 24/1: pin connector with snap-in locking device (STOCKO) 8 poles, pitch 2.5 mm	
249637	Adapter for DEC 24/1: screw terminal 8 poles, pitch 2.54 mm, AWG 20 - 26	

Various		Page
235811	Shunt regulator 12-75 VDC (adjustable), P <sub>max</sub> 475 W, P <sub>cont</sub> 25 W, module housing 180 x 103 x 26 mm	
309687	Shunt regulator 27 VDC or 56 VDC (selectable), P <sub>max</sub> 300 W, P <sub>cont</sub> 10 W	