



RC Standard marker cards

Each marker card contains 10 strips of 10 markers, i.e. 100 markers per card.


Marker cards are white polyamide 6 with black lettering.



Horizontal marker See page 1930 for most popular.




Vertical marker See page 1933 for most popular.




Top marking See page 1937.

How to use




1

Remove one of the side bands of the card.



2

Separate the chosen strip from the rest of the card.



3

- Strips of 10 markers for block spacings 5 mm .197", 6 mm .236" and 8 mm .315": Press the first marker in place, hold it and slide your thumb on the rest of the strip to snap each marker on the terminal block assembly.
- Single markers : Press the chosen marker in place, hold it and tear off the rest of the strip.

Marker sizes

RC55
5 x 5 mm markers
.197" x .197".
Can be used on blocks from 5 mm .197" spacing, with possibility of mounting 2 markers per slot.

RC65
6 x 5 mm markers
.236" x .197".
Can be used on blocks from 6 mm .236" spacing, with possibility of mounting 2 markers per slot.

RCAL85
8 x 5 mm markers
.315" x .197".
Can be used on 8 mm .315" spacing spring connection blocks & mini ADO blocks.

RC410
4 x 10 mm markers
.157" x .394".
Can be used on blocks from 4 mm .157" spacing, 1 marker per slot.

RC510
5 x 10 mm markers
.197" x .394".
Can be used on blocks from 5 mm .197" spacing, 1 marker per slot.

RC610
6 x 10 mm markers
.236" x .394".
Can be used on blocks from 6 mm .236" spacing, 1 marker per slot.


RC810
8 x 10 mm markers
.315" x .394".
Can be used on blocks from 8 mm .315" spacing, 1 marker per slot.

RC1010
10 x 10 mm markers
.394" x .394".
Can be used on blocks from 10 mm .394" spacing, 1 marker per slot.

The marker that goes into the terminal block slot for each marking method is listed here :

Marker	Marking method
RC410	⇒ ③
RC55	⇒ ⑤ ⑩
RC510	⇒ ⑥ ⑩
RC65	⇒ ⑤ ⑪
RC610	⇒ ⑥ ⑪
RCAL85	⇒ ⑫
RC810	⇒ ⑰
RC1010	⇒ ⑳

Standard marker cards	Marker width mm	Marker height, L mm	Use with terminal block thickness
RC410	4	10	4 mm
RC55	5	5	5 mm
RC510	5	10	5 mm
RC65	6	5	6 mm
RC610	6	10	6 mm
RCAL85	8	5	8 mm
RC810	8	10	8 mm and larger
RC1010	10	10	10 mm and larger




Blank marker cards	RC410	RC55	RC510	RC65
	white 0229 000.15	white 0230 000.12	white 0231 000.07	red 0103 776.01 blue 0103 775.00 white 0232 000.00
	RC610	RCAL85	RC810	
	white 0233 000.01 green 0206 230.11 yellow 0206 231.06 orange 0206 232.07	blue 0206 233.00 purple 0206 234.01 red 0206 235.02	white 0237 000.05	white 0234 000.02
	RC1010			white 0238 000.16
Mürplastik markers for terminal blocks	RC510A white 0231 500.01	RC610A white 0233 500.03	RC810A white 0234 500.04	

Card holder for item above 0205 462.05

RC Standard marker cards (cont.)

Horizontal marking of numbers (cont.)

MOST POPULAR



For vertical markers, see page 1933.

1	2	3	4	5	6	7	8	9	10
11	12	13	14	15	16	17	18	19	20
21	22	23	24	25	26	27	28	29	30

Horizontal marking
Increasing order

RCAL85

1 → 100 **0237 030.22**

See page 1936.

RC55	RC510	RC65	RC610	RC810	RC1010
1 → 100 0230 030.07	1 → 100 0231 030.24	1 → 100 0232 030.25	1 → 100 0233 030.26	1 → 100 0234 030.27	1 → 80 0238 030.03
101 → 200 0230 031.24	101 → 200 0231 031.11	101 → 200 0232 031.12	101 → 200 0233 031.13	101 → 200 0234 031.14	81 → 160 0238 031.20
201 → 300 0230 032.25	201 → 300 0231 032.12	201 → 300 0232 032.13	201 → 300 0233 032.14	201 → 300 0234 032.15	161 → 240 0238 032.21
301 → 400 0230 033.26	301 → 400 0231 033.13	301 → 400 0232 033.14	301 → 400 0233 033.15	301 → 400 0234 033.16	241 → 320 0238 033.22
401 → 500 0230 034.34	401 → 500 0231 034.14	401 → 500 0232 034.15	401 → 500 0233 034.16	401 → 500 0234 034.17	321 → 400 0238 034.23
501 → 600 0230 035.20	501 → 600 0231 035.15	501 → 600 0232 035.16	501 → 600 0233 035.17	501 → 600 0234 035.10	401 → 480 0238 035.24
601 → 700 0230 036.21	601 → 700 0231 036.16	601 → 700 0232 036.17	601 → 700 0233 036.10	601 → 700 0234 036.11	481 → 560 0238 036.25
701 → 800 0230 037.22	701 → 800 0231 037.17	701 → 800 0232 037.10	701 → 800 0233 074.26	701 → 800 0234 037.12	561 → 640 0238 037.26
801 → 900 0230 038.03	801 → 900 0231 038.20	801 → 900 0232 038.21	801 → 900 0233 075.27	801 → 900 0234 038.23	641 → 720 0238 038.07
901 → 1000 0230 039.04	901 → 1000 0231 039.21	901 → 1000 0232 039.22	901 → 1000 0233 076.20	901 → 1000 0234 039.24	721 → 800 0238 039.00
1001 → ... 0230 071.04*	1001 → ... 0231 071.21*	1001 → ... 0232 071.22*	1001 → ... 0233 073.25*	1001 → ... 0234 071.24*	801 → 880 0238 040.15
					881 → 960 0238 041.02

* Part numbers identical for each group of numbers : on request (indicate marking). Ex. : 0230 071.04 : 1001 to 1100.

8	8	8	8	8	8	8	8	8	8
8	8	8	8	8	8	8	8	8	8
8	8	8	8	8	8	8	8	8	8

Horizontal marking
Repeated identical numbers

Markers	Marking method	Marker width mm	Marker height, L mm	Use with terminal blocks thickness
RC55	⑤ ⑩	5	5	5 mm
RC510	⑥ ⑩	5	10	5 mm
RC65	⑤ ⑪	6	5	6 mm
RC610	⑥ ⑪	6	10	6 mm
RC810	⑰	8	10	8 mm
RC1010	⑳	10	10	10 mm and larger

RC55	RC510	RC65	RC610
100 x 0 0230 240.26	100 x 0 0231 210.05	100 x 0 0232 201.02	100 x 0 0233 201.03
100 x 1 0230 241.13	100 x 1 0231 211.22	100 x 1 0232 202.03	100 x 1 0233 202.04
100 x 2 0230 242.14	100 x 2 0231 212.23	100 x 2 0232 203.04	100 x 2 0233 203.05
100 x 3 0230 243.15	100 x 3 0231 213.24	100 x 3 0232 204.05	100 x 3 0233 204.06
100 x 4 0230 244.16	100 x 4 0231 214.25	100 x 4 0232 205.06	100 x 4 0233 205.07
100 x 5 0230 245.17	100 x 5 0231 215.26	100 x 5 0232 206.07	100 x 5 0233 206.00
100 x6 or 9 0230 246.10	100 x6 or 9 0231 216.27	100 x6 or 9 0232 207.00	100 x6 or 9 0233 207.01
100 x 7 0230 247.11	100 x 7 0231 217.20	100 x 7 0232 208.11	100 x 7 0233 208.12
100 x 8 0230 248.22	100 x 8 0231 218.01	100 x 8 0232 209.12	100 x 8 0233 209.13
100 x 10 0230 250.20	100 x 10 0231 220.07	100 x 10 0232 211.23	100 x 10 0233 211.24
100 x 11 0230 251.15	100 x 11 0231 221.24	100 x 11 0232 212.24	100 x 11 0233 212.25
100 x 12 0230 252.16	100 x 12 0231 222.25	100 x 12 0232 213.25	100 x 12 0233 213.26
100 x 13 0230 253.17	100 x 13 0231 223.26	100 x 13 0232 214.26	100 x 13 0233 214.27
100 x 14 0230 254.10	100 x 14 0231 224.27	100 x 14 0232 215.27	100 x 14 0233 215.20
100 x 15 0230 255.11	100 x 15 0231 225.20	100 x 15 0232 216.20	100 x 15 0233 216.21
100 x 16 0230 256.12	100 x 16 0231 226.21	100 x 16 0232 217.21	100 x 16 0233 217.22
100 x 17 0230 257.13	100 x 17 0231 227.22	100 x 17 0232 218.02	100 x 17 0233 218.03
100 x 18 0230 258.24	100 x 18 0231 228.03	100 x 18 0232 219.03	100 x 18 0233 219.04
100 x 19 0230 259.25	100 x 19 0231 229.04	100 x 19 0232 220.00	100 x 19 0233 220.01
100 x 20 0230 260.22	100 x 20 0231 230.01	100 x 20 0232 221.25	100 x 20 0233 221.26
	100 x .. } 0231 231.26* 999	100 x .. } 0232 222.26* 999	100 x .. } 0233 222.27* 999

* Part numbers identical for each group of numbers : on request (indicate marking). Ex. : 0231 231.26 : 100 x 21.