



LOGO!POWER 24 V/2.5 A STABILIZED POWER SUPPLY
INPUT: 100-240 V AC (110-300 V DC) OUTPUT: 24 V/2.5 A DC

Technical specifications

Product	LOGO!Power
Power supply, type	24 V/2.5 A
Input	
Input	1-phase AC or DC
Supply voltage / at AC / nominal value min.	100 V
Supply voltage / at AC / nominal value max.	240 V
Supply voltage	
• at AC	85 ... 264 V
Input voltage / at DC	110 ... 300 V
Wide-range input	Yes
Overvoltage resistance	$2.3 \times V_{in}$ rated, 1.3 ms
Mains buffering at I _{out} rated, min.	40 ms
Mains buffering	at $V_{in} = 187$ V
Rated line frequency	50 / 60 Hz
Rated line range	47 ... 63 Hz
Input current / at nominal level of the input voltage 120 V	1.22 A
Input current / at nominal level of the input voltage 230 V	0.66 A
Switch-on current limiting (+25 °C), max.	46 A
I ² t, max.	3 A ² ·s
Built-in incoming fuse	internal

Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 16 A characteristic B or from 10 A characteristic C
Output	
Output	Controlled, isolated DC voltage
Rated voltage Vout DC	24 V
Total tolerance, static $\pm$	3 %
Static mains compensation, approx.	0.1 %
Static load balancing, approx.	1.5 %
Residual ripple peak-peak, max.	200 mV
Residual ripple peak-peak, typ.	10 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	300 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	50 mV
Adjustment range	22.2 ... 26.4 V
Product feature / output voltage adjustable	Yes
Output voltage setting	via potentiometer
Status display	Green LED for output voltage OK
On/off behavior	No overshoot of Vout (soft start)
Startup delay, max.	0.5 s
Voltage rise, typ.	10 ms
Rated current value Iout rated	2.5 A
Current range	0 ... 2.5 A
• Note	+55 ... +70 °C: Derating 2%/K
delivered active power / typ.	60 W
Parallel switching for enhanced performance	Yes
Numbers of parallel switchable units for enhanced performance	2
Efficiency	
Efficiency at Vout rated, Iout rated, approx.	88 %
Power loss at Vout rated, Iout rated, approx.	8 W
Effective power loss / at idle / maximum	1.8 W
Closed-loop control	
Dynamic mains compensation (Vin rated ± 15 %), max.	0.2 %
Dynamic load smoothing (Iout: 10/90/10 %), Uout $\pm$ typ.	2 %
Load step setting time 10 to 90%, typ.	1 ms
Load step setting time 90 to 10%, typ.	1 ms
Protection and monitoring	
Output overvoltage protection	Yes, according to EN 60950-1
Current limitation, typ.	3.3 A
Characteristic feature of the output / short-circuit protected	Yes
Short-circuit protection	Constant current characteristic

Enduring short circuit current / Effective level / maximum	4.8 A
Overload/short-circuit indicator	-
Safety	
Primary/secondary isolation	Yes
Potential separation	Safety extra-low output voltage U _{out} acc. to EN 60950-1 and EN 50178
Protection class	Class II (without protective conductor)
CE mark	Yes
UL/CSA approval	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus-Recognized (UL 60950, CSA C22.2 No. 60950), File E151273, NEC class 2 (acc. to UL 1310)
Explosion protection	ATEX (EX) II 3G Ex nA IIC T3; cCSAus (CSA C22.2 No. 213-M1987, ANSI/ISA-12.12.01-2007) Class I, Div. 2, Group ABCD, T4
FM approval	Class I, Div. 2, Group ABCD, T4
CB approval	Yes
Marine approval	GL, ABS, BV, DNV, LRS
Degree of protection (EN 60529)	IP20
EMC	
Emitted interference	EN 55022 Class B
Supply harmonics limitation	not applicable
Noise immunity	EN 61000-6-2
Operating data	
Ambient temperature / in operation	-20 ... +70 °C
• Note	with natural convection
Ambient temperature / on transport	-40 ... +85 °C
Ambient temperature / in storage	-40 ... +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation
Mechanics	
Connection technology	screw-type terminals
Connections / Supply input	L, N: 1 screw terminal each for 0.5 ... 2.5 mm ² single-core/finely stranded
Connections / Output	+, -: 2 screw terminals each for 0.5 ... 2.5 mm ²
Connections / Auxiliary	-
Width / of the housing	72 mm
Height / of the housing	90 mm
Depth / of the housing	52.6 mm
Installation width	72 mm
Mounting height	130 mm
Weight, approx.	0.25 kg
Product feature / of the housing / housing for side-by-side mounting	Yes

Mounting type / wall mounting	No
Type of mounting / standard rail mounting	Yes
Mounting type / S7 rail mounting	No
Installation	Snaps onto DIN rail EN 60715 35x7.5/15
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)

letzte Änderung:

Aug 8, 2014