

Distinctive Characteristics

Optional caps in different colors to vary appearance as needed.

Low operating force for ease of actuation.

Rear panel bushing mount with compact behind panel dimension.

Internal antijamming feature to protect the contacts from damage due to excessive force on the plunger.

Self-cleaning contacts make FB models highly reliable.


Low cost device of rugged one-piece bushing and housing construction.

Reliability of construction with an internal guide to maintain contact alignment.

Epoxy sealed terminals.



Actual Size



General Specifications

Electrical Capacity (Resistive Load)

Power Level: 500mA @ 125V AC for silver
Logic Level: 0.4VA max. @ 28V AC/DC max. for gold
 Note: See Supplement Index (page Z2) to find explanation of operating range.

Other Ratings

Contact Resistance: 30 milliohms maximum for silver;
 30 milliohms maximum for gold
Insulation Resistance: 100 megohms minimum @ 500V DC
Dielectric Strength: 1,000V AC minimum between contacts
 & between contacts & case for 1 minute minimum
Mechanical Life: 50,000 operations minimum
Electrical Life: 50,000 operations minimum
Nominal Operating Force: 220 grams
Travel: 1.1mm (.043") Pretravel;
 0.57mm (.022") Overtravel;
 1.67mm (.065") Total travel

Materials & Finishes

Plunger: Polyacetal
Bushing: Brass with nickel plating
Case: Phenolic resin
Movable Contactor: Copper with silver or gold plating
Stationary Contacts: Phosphor bronze with silver or gold plating
Terminals: Phosphor bronze with silver or gold plating

Environmental & Installation Data


Operating Temp Range: -10°C through +70°C (+14°F through +158°F)
Soldering Time & Temperature: 5 seconds @ 270°C

Standards & Certifications

UL Recognized: Models rated 0.5A @ 125V AC Single pole: Momentary action circuit with solder lug terminations. UL File Number: WOYR2.E44145; add "/U" to end of part number to order UL mark on switch.



TYPICAL SWITCH ORDERING EXAMPLE



DESCRIPTION FOR TYPICAL ORDERING EXAMPLE

FB15ANEP2-FA



POLES & CIRCUITS

Pole	Model	Plunger Position () = Momentary		Connected Terminals		Throw & Schematic
		Normal	Down	Normal	Down	
SP	FB15AN	OFF	(ON)	OPEN	1-2	SPST

Note: Terminal numbers are not actually on the switch.

TERMINALS

EP Epoxy Sealed
PC/Turret Terminals


P No Epoxy
PC/Turret Terminals

CONTACT MATERIALS & RATINGS

2 Silver Contacts	Power Level	500mA @ 125V AC
4 Gold Contacts	Logic Level	0.4VA maximum @ 28V AC/DC maximum

TYPICAL SWITCH DIMENSIONS

PC/Turret




FB15ANEP2-FA

Plunger is white polyacetal.

OPTIONAL SLIP-ON CAPS & COLORS


F AT475
.201" Diameter

Material: Polyamide
Finish: Glossy



H AT496
.295" Diameter

Material: Polyamide
Finish: Glossy



Colors Available:

A Black


B White

C Red

STANDARD HARDWARE & PANEL CUTOUT

AT536 Hex Nut

Material:
Brass with nickel plating



Panel Thickness:

2.8mm (.110") maximum

