

Inline terminal - IB IL AI 2/4-20-PAC - 2862217

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Terminal with two analog inputs



Product description

The terminal is designed for use within an Inline station. It serves to measure voltage or current signals.


Features

- Two analog single-ended signal inputs for the connection of either voltage or current signals
- Connection of the sensors using the 2 or 3-wire system
- Three current measuring ranges: 0 mA to 20 mA, ±20 mA, 4 mA to 20 mA
- Two voltage measuring ranges: 0 V to 10 V, ±10 V
- Presetting of both channels to measuring range of 4 mA to 20 mA
- Configuration of the channels independently of one another via INTERBUS
- Measured values can be displayed in four different formats

Why buy this product

- 2 analog single-ended signal inputs for the connection of either voltage or current signals
- Connection of sensors in 2 and 3-wire technology
- Current ranges: 0 mA ... 20 mA, 4 mA ... 20 mA, ±20 mA
- Measured values can be represented in four different formats
- Voltage ranges: 0 V ... 10 V, ±10 V

Key commercial data

Packing unit	1 pc
GTIN	 4 017918 910044
Weight per Piece (excluding packing)	93.7 g
Custom tariff number	85389091
Country of origin	Germany

Technical data

Note:

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	12.2 mm
Height	136.8 mm
Depth	71.5 mm

Inline terminal - IB IL AI 2/4-20-PAC - 2862217

Technical data

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	10 % ... 95 % (according to DIN EN 61131-2)
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Degree of protection	IP20

General

Weight	47 g
Mounting type	DIN rail
Protection class	III, IEC 61140, EN 61140, VDE 0140-1

Interfaces

Fieldbus system	Lokalbus
Name	Inline local bus
Connection method	Inline data jumper
Transmission speed	500 kBit/s
Transmission physics	Copper

Inline potentials

Communications power U_L	7.5 V DC
Current consumption from U_L	max. 60 mA
	typ. 45 mA
I/O supply voltage U_{ANA}	24 V DC
Current consumption from U_{ANA}	max. 18 mA
	typ. 13.5 mA

Analog inputs

Number of inputs	max. 2 (single ended)
Connection method	Inline shield connector
	2-wire (shielded)
Input name	Analog inputs
Current input signal	0 mA ... 20 mA
	4 mA ... 20 mA
	-20 mA ... 20 mA
Voltage input signal	0 V ... 10 V
	-10 V ... 10 V
Number of inputs	4 (single-ended voltage inputs)
Voltage input signal	0 V ... 10 V
	-10 V ... 10 V
Number of inputs	4 (single-ended current inputs)
Current input signal	0 mA ... 20 mA

Inline terminal - IB IL AI 2/4-20-PAC - 2862217

Technical data

Analog inputs

	4 mA ... 20 mA
	-20 mA ... 20 mA

Classifications

eCl@ss

eCl@ss 4.0	27250303
eCl@ss 4.1	27250303
eCl@ss 5.0	27250303
eCl@ss 5.1	27242601
eCl@ss 6.0	27242601
eCl@ss 7.0	27242601
eCl@ss 8.0	27242601

ETIM

ETIM 2.0	EC001431
ETIM 3.0	EC001596
ETIM 4.0	EC001596
ETIM 5.0	EC001596

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / cULus Recognized


Ex Approvals


Approvals submitted


Approval details

Inline terminal - IB IL AI 2/4-20-PAC - 2862217

Approvals

UL Recognized 

cUL Recognized 

cULus Recognized 

Accessories

Accessories

Labeling panel

Labeling field - IB IL FIELD 2 - 2727501

Labeling field, width: 12.2 mm



Plug

Inline shield connector - IB IL SCN 6-SHIELD-TWIN - 2740245



Inline shield connector

Inline shield connector - IB IL SCN-6 SHIELD - 2726353



Inline shield connector

Terminal marking

Inline terminal - IB IL AI 2/4-20-PAC - 2862217

Accessories

Insert strip - ESL 62X10 - 0809492

Insert strip, Sheet, white, Unlabeled, Can be labeled with: Office printing systems, Plotter: Laser printer, Mounting type: Insert, Lettering field: 62 x 10 mm



Phoenix Contact 2014 © - all rights reserved
<http://www.phoenixcontact.com>