

6867 AGM-204-500

General Information

Extended Product Type:	6867 AGM-204-500
Product ID:	6800-0-2554
EAN:	4011395150887
Catalog Description:	6867 AGM-204-500
Long Description:	Electronic movement detector for detecting thermal motion. Remote control possible via IR remote control 6841 (included in delivery). With display for detection and operation mode. With ground and rear-field detection. With high-quality lens for optimum detection. Surveillance density: 110 sectors with 440 switching segments. All functions controlled by microprocessor. Continuous light (4 hours) and presence simulation can be activated via remote control. With automatic range stabilization. With automatic interference suppression. With automatic dazzle-proofing. With brightness-independent test mode for evaluating the detection zone. Additional possibility for switch-on via normally open push-button switch. Switch-off delay: 10 sec to 30 min or short-time pulse 1 sec adjustable. Electronic movement detector for detecting thermal motion. Remote control possible via IR remote control 6841 (included in delivery). With display for detection and operation mode. With ground and rear-field detection. With high-quality lens for optimum detection. Surveillance density: 110 sectors with 440 switching segments. All functions controlled by microprocessor. Continuous light (4 hours) and presence simulation can be activated via remote control. With automatic range stabilization. With automatic interference suppression. With automatic dazzle-proofing. With brightness-independent test mode for evaluating the detection zone. Additional possibility for switch-on via normally open push-button switch. Switch-off delay: 10 sec to 30 min or short-time pulse 1 sec adjustable.

Additional Information

Catalog Description:	6867 AGM-204-500
Country of Origin:	Germany (DE)
Customs Tariff Number:	85365080
EAN:	4011395150887
Environmental Information:	9AKK104295D8727
Invoice Description:	6867 AGM-204-500
Long Description:	Electronic movement detector for detecting thermal motion. Remote control possible via IR remote control 6841 (included in delivery). With display for detection and operation mode. With ground and rear-field detection. With high-quality lens for optimum detection. Surveillance density: 110 sectors with 440 switching segments. All functions controlled by microprocessor. Continuous light (4 hours) and presence simulation can be activated via remote control. With automatic range stabilization. With automatic interference suppression. With automatic dazzle-proofing. With brightness-independent test mode for evaluating the detection zone. Additional possibility for switch-on via normally open push-button switch. Switch-off delay: 10 sec to 30 min or short-time pulse 1 sec adjustable. Electronic movement detector for detecting thermal motion. Remote control possible via IR remote control 6841 (included in delivery). With display for detection and operation mode. With ground and rear-field detection. With high-quality lens for optimum detection. Surveillance density: 110 sectors with 440 switching segments. All functions controlled by microprocessor. Continuous light (4 hours) and presence simulation can be activated via remote control. With automatic range stabilization. With automatic interference suppression. With automatic dazzle-proofing. With brightness-independent test mode for evaluating the detection zone. Additional possibility for switch-on via normally open push-button switch. Switch-off delay: 10 sec to 30 min or short-time pulse 1 sec adjustable.
Minimum Order Quantity:	1 piece
Package Level 1 Height:	0.145 m
Package Level 1 Length:	0.179 m
Package Level 1 Units:	1 piece
Package Level 1 Width:	0.165 m
Package Level 2 Height:	0.305 m
Package Level 2 Length:	0.367 m
Package Level 2 Units:	8 piece
Package Level 2 Width:	0.339 m
Package Level 3 Height:	1.065 m
Package Level 3 Length:	1.2 m
Package Level 3 Units:	144 piece
Package Level 3 Width:	0.8 m
Product Main Type:	Surface-mounted devices
RoHS Status:	No declaration needed
Selling Unit of Measure:	piece
Suitable for Product Class:	Electronics