

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [39-00-0120](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit Jr.™ Power Connectors](#)  
**Description:** Mini-Fit® Male Crimp Terminal, Tin (Sn) Plated Brass Contact, 18-24 AWG, Reel

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary TS-5556-002 (PDF)</a>
<a href="#">Product Specification PS-5556-002 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Packaging Specification PK-5558-001 (PDF)</a>	

**General**

Product Family	Crimp Terminals
Series	5558
Application	Power
Crimp Quality Equipment	Yes
Overview	<a href="#">Mini-Fit Jr.™ Power Connectors</a>
Product Name	Mini-Fit®
UPC	800754395151

**Physical**

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.126/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

**Electrical**


Current - Maximum per Contact	9A
Voltage - Maximum	600V

**Material Info**

Old Part Number	5558-S
-----------------	--------

**Reference - Drawing Numbers**

Packaging Specification	PK-5558-001
Product Specification	PS-5556-002
Sales Drawing	SD-5558-*S*
Test Summary	TS-5556-002



**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC  
Contains SVHC: No  
Low-Halogen Status  
Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[5558Series](#)

**Mates With**

[5556](#) Mini-Fit® Crimp Terminal

**Use With**

[5559](#) Mini-Fit Jr.™ Plug Housing, [30068](#) Mini-Fit® TPA Plug Housing, [42475](#) Mini-Fit® BMI Plug Housing

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	<a href="#">0638190900</a>
FineAdjust™ Applicator for	<a href="#">0639023900</a>

Insulation OD  
 1.40-1.70mm - 18-24  
 AWG  
 T2 Terminator™ for 0639102900  
 insulation OD 1.65  
 – 2.05mm – 18 – 24  
 AWG  
 T2 Terminator™ 0639123900  
 for insulation OD  
 1.40-1.70mm - 18-24  
 AWG  
 FineAdjust™ 0639024800  
 Applicator for  
 Insulation OD  
 2.50-2.95mm  
 Optimized for 18  
 AWG Only  
 T2 Terminator™ 0639115600  
 for insulation OD  
 1.90-2.30mm - 18-24  
 AWG  
 Extraction Tool 0011030044  
 FineAdjust™ 0639002600  
 Applicator for  
 Insulation OD  
 2.50-2.95mm - 18-24  
 AWG  
 FineAdjust™ 0639002900  
 Applicator for  
 Insulation OD  
 1.65-2.05mm - 18-24  
 AWG  
 T2 Terminator™ 0639102600  
 for insulation OD  
 2.50-2.95mm - 18-24  
 AWG  
 T2 Terminator™ 0639124800  
 for insulation OD  
 2.50-2.95mm  
 optimized for 18  
 AWG only  
 FineAdjust™ 0639015600  
 Applicator for  
 Insulation OD  
 1.90-2.30mm - 18-24  
 AWG  
 FineAdjust™ 0639024900  
 Applicator for  
 Insulation OD  
 2.30-2.60mm - 18-24  
 AWG  
 T2 Terminator™ 0639124900  
 for insulation OD  
 2.30-2.60mm - 18-24  
 AWG

This document was generated on 02/11/2015

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**