

E

D

C

B

A

E




D

C

B

A

MATERIAL NUMBER	OLD PART NUMBER	COUPLING NUT MATERIAL	COUPLING NUT FINISH
130017-0008	1A3002-34	BRASS	NICKEL PLATED
130017-0009	1A3002-348	STAINLESS STEEL	PASSIVATED



MALE FACE VIEW

1	_____
2	_____
3	_____

WIRING CHART

VOLTAGE RATING	600VAC/VDC
AMPERAGE RATING	13 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 80°C
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	NYLON	BLACK
2	PIN CONTACTS	COPPER ALLOY	GOLD PLATED
3	O-RING	NITRILE	BLACK
4	COUPLING NUT	SEE CHART	SEE CHART
5	MOLDED BODY	NYLON	BLACK
6	GROMMET	NITRILE	BLACK
7	CORD GRIP BODY	NYLON	BLACK

EC NO: WNA2010-0067	7/29/09
DRWN: BWOODMAN	
CHKD: JM	
APPR: JFMURPHY	2009/08/10
REV	
A	

QUALITY SYMBOLS
$\nabla=0$
$\nabla C=0$

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	±----	±----
3 PLACES	±----	±----
2 PLACES	±----	±.01
1 PLACE	±0.3	±----
ANGULAR ±----°		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE IN/MM	
DRAWN BY	DATE
BW	2009/07/28
CHECKED BY	DATE
TW	2009/07/29
APPROVED BY	DATE
---	---
MATERIAL NO.	SEE CHART
SIZE	A

SCALE -----	DESIGN UNITS -----	 THIRD ANGLE PROJECTION
TITLE		
MINI 3P MALE ATTACH INT .20-.48 O.D. CABLE RANGE -----		
MOLEX INCORPORATED		
DOCUMENT NO. SD-130017-004		SHEET NO. 1 OF 1
CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX		

6

5

4

3

2

1