



ENGLISH

Datasheet

Noga S10 Deburring Blades

RS Stock No: 244-6773




Specifications:

Noga S10 Blade

Right hand cutting

For use on Steel, Aluminium and Plastic

Pack quantity: 10



Order Code	S10
Included Angle	40°
Blade Material	HSS M2
Blade Hardness	62 – 64 HRC
L: Overall Length	48mm
L1: Length Inside Handle	28mm
L2: Protrusion from Handle Length	20mm
L3: Cutting Length	6mm
D: Shank Diameter	3.2mm

Order Code	Manufacturers Code	Product Description
244-6773	S10	Noga S10 Blades