


SFB 400/10

Sinusoidal filter

- Possibility of long shielded motor cables*
- High life expectancy and low noise of the connected motor

Output filter with capacitor for frequency inverter to IEC 61558-2-20, DIN EN 61558-2-20, VDE 0570 part 2-20

*200 m up to 520 V line voltage, 400 m up to 230 V line voltage



Dimensions in mm



SFB 400/10

Sinusoidal filter



Input data	
Rated voltage	3 x 400 V
Voltage range	up to 3 x 520 V
Voltage drop	typ. 3 x 30 V
Rated current	10.00 A
Frequency range	0 - 120 Hz
Output data	
for motor rated output approx.	4.00 kW
for inverter output approx.	6.90 kVA
Standards and security	
Approvals	C-UL-US
Protection index	IP 00
Safety class (prepared)	I
Ambient temperature max.	40 °C
Class of Insulation System	F
Test voltage	3000 V, 50 Hz
General data	
Application	suitable for installation in equipments and systems
Switching frequency	3 - 8 kHz
Mechanical data	
Type	open type
Terminals	screw-type terminals
Wire range	4 mm ²
Fixing screws	M5
Weight	5.50 kg
Order numbers	
Order Number	SFB 400/10

BLOCK Transformatoren-Elektronik GmbH

Max-Planck-Straße 36-46

27283 Verden

Germany

Phone +49 4231 678-0

Fax +49 4231 678-177