


Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG
RF_35/08.13/6.1

Technical Data Sheet		Rosenberger																																	
BNC 75 Ω	STRAIGHT JACK	71K101-109N5																																	
 All dimensions are in mm; tolerances according to ISO 2768 m-H <table><tr><td colspan="3">Interface</td></tr><tr><td>Compatible to</td><td colspan="2">IEC 61169-8, MIL-PRF-39012, CECC 22120</td></tr><tr><td colspan="3">Documents</td></tr><tr><td>Assembly instruction</td><td colspan="2">51 P</td></tr><tr><td colspan="3">Material and plating</td></tr><tr><td>Connector parts</td><td>Material</td><td>Plating</td></tr><tr><td>Center contact</td><td>Spring bronze</td><td>AuroDur®, gold plated</td></tr><tr><td>Outer contact</td><td>Brass</td><td>Flash white bronze over silver(e.g. Optargen®)</td></tr><tr><td>Body</td><td>Brass</td><td>Flash white bronze over silver(e.g. Optargen®)</td></tr><tr><td>Dielectric</td><td>PTFE</td><td></td></tr><tr><td>Crimping ferrule</td><td>Copper</td><td>Flash white bronze over silver(e.g. Optargen®)</td></tr></table>			Interface			Compatible to	IEC 61169-8, MIL-PRF-39012, CECC 22120		Documents			Assembly instruction	51 P		Material and plating			Connector parts	Material	Plating	Center contact	Spring bronze	AuroDur®, gold plated	Outer contact	Brass	Flash white bronze over silver(e.g. Optargen®)	Body	Brass	Flash white bronze over silver(e.g. Optargen®)	Dielectric	PTFE		Crimping ferrule	Copper	Flash white bronze over silver(e.g. Optargen®)
Interface																																			
Compatible to	IEC 61169-8, MIL-PRF-39012, CECC 22120																																		
Documents																																			
Assembly instruction	51 P																																		
Material and plating																																			
Connector parts	Material	Plating																																	
Center contact	Spring bronze	AuroDur®, gold plated																																	
Outer contact	Brass	Flash white bronze over silver(e.g. Optargen®)																																	
Body	Brass	Flash white bronze over silver(e.g. Optargen®)																																	
Dielectric	PTFE																																		
Crimping ferrule	Copper	Flash white bronze over silver(e.g. Optargen®)																																	
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de		Tel. : +49 8684 18-0 Fax : +49 8684 18-499 Email : info@rosenberger.de																																	
		Page 1 / 2																																	

Technical Data Sheet				Rosenberger			
BNC 75 Ω		STRAIGHT JACK		71K101-109N5			
Electrical data Impedance75 Ω FrequencyDC to 4 GHz Return loss≥ 23 dB @ DC to 1 GHz ≥ 15 dB @ 1 GHz to 4 GHz Insertion loss≤ 0.05 x √ f [GHz] dB Insulation resistance≥ 5 GΩ Center contact resistance≤ 1.5 mΩ Outer contact resistance≤ 1 mΩ Test voltage (at sea level)1500 V rms Working voltage (at sea level)400 V rms Power handling (at 20 °C, sea level, VSWR 1.0)80 W @ 2 GHz - Limitations are possible due to the used cable type - Mechanical data Mating cycles≥ 500 Center contact captivation: axial≥ 15 N Environmental data Temperature range-45 °C to +85 °C Thermal shockMIL-STD-202, Method 107, Condition B Corrosion resistanceMIL-STD-202, Method 101, Condition B VibrationMIL-STD-202, Method 204, Condition B ShockMIL-STD-202, Method 213, Condition G Moisture resistanceMIL-STD-202, Method 106 RoHScompliant Tooling Crimping tool11W150-000 Crimp insert11W150-209 Suitable cables RG 59 B/U Packing Standard1 pce in bag Weight13.5 g/pce							
While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.							
Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Inge Mühlauer	20.07.04	A. Gasteiger	06.08.13	c00	07-0154	J. Krautenbacher	06.08.13
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Fax : +49 8684 18-499 Email : info@rosenberger.de			Page 2 / 2