

### General Information

Extended Product Type:	BJMI5-3
Product ID:	1SNA176279R1700
EAN:	3472591762792
Catalog Description:	BJMI5-3 POLES Jumper Bars
Long Description:	BJMI5-3 - Jumper Bars - 3 poles -- 5mm Spacing

### Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

### Ordering

EAN:	3472591762792
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

### Dimensions

Product Net Weight:	5 g
---------------------	-----

### Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	155 mm
Package Level 1 Height:	5 mm
Package Level 1 Length:	200 mm
Package Level 1 Gross Weight:	0.05 kg
Package Level 1 EAN:	3472591762792
Package Level 2 Units:	500 piece
Package Level 3 Units:	90000 piece
Product Packing Type:	Bag

### Additional Information

Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Function:	Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Mounting Type:	Fractionable model, composed of captive screws on a jumper bar, with IP20 protection touchproof. This accessory can be used for connecting consecutive blocks only.
Product Main Type:	BJMI
Product Name:	Jumper Bar
Rated Current (I <sub>n</sub> ):	Main Circuit 24 A
Spacing:	5 mm
Sub-Function:	Assembled jumper bar
Sub-Function 2:	Screw
Suitable For:	D1.5/5.ADO.NF D1/5.ADO D1/5.D2.ADO D2.5/5.ADO D2.5/5.D2.ADO MA2.5/5 MA2.5/5-2CPE MA2.5/5-CPE MA2.5/5D-2CPE

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SNC160001C0207-CH-J Accessories
Declaration of Conformity - CE:	1SND225001C1009
RoHS Information:	1SND230492F0201

### Classifications

ETIM 4.0:	EC000489 - Cross-connector for terminal block
ETIM 5.0:	EC000489 - Cross-connector for terminal block
Object Classification Code:	X

