

Printed-circuit board connector - PST 1,0/12-H-3,5 - 1737116

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 8 A, Rated voltage (III/2): 250 V, Number of positions: 12, Pitch: 3.5 mm, Color: black, Contact surface: Tin, Mounting: Soldering, The maximum current depends on the plug used. The lower of the two current values apply for plug and pin strip. The pin strip is made of highly temperature resistant plastic and is thus suitable for the reflow process.




The figure shows a 10-position version of the product

Why buy this product

- Various pin lengths and pin geometries available on request
- Pin strip with pad pushed on for suction pipette for optional tape-on-reel packing
- 3.5 mm pitch
- Pin strip available in machine-capable packaging (tube magazine or tape)
- Optimum pin geometry so as to not damage the plug
- Reflow solderable pin strip, optimized for COMBICON compact connectors



Key commercial data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 183529
Weight per Piece (excluding packing)	1.7 g
Custom tariff number	85366990
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length	10.5 mm
Pitch	3.5 mm
Dimension a	38.5 mm
Pin dimensions	1 mm
Hole diameter	1.2 mm

General

Printed-circuit board connector - PST 1,0/12-H-3,5 - 1737116

Technical data

General

Range of articles	PST 1,0/...-H
Insulating material group	IIIa
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	160 V
Rated voltage (III/2)	250 V
Rated voltage (II/2)	250 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	8 A (depends on the plug used)
Maximum load current	8 A (depends on the plug used)
Insulating material	PA
Inflammability class according to UL 94	V0
Color	black
Number of positions	12

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211801
UNSPSC 7.0901	39121432
UNSPSC 11	34131203
UNSPSC 12.01	39121432
UNSPSC 13.2	39121432

Approvals

Approvals

Printed-circuit board connector - PST 1,0/12-H-3,5 - 1737116

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

UL Recognized	
	B
Nominal current I _N	10 A
Nominal voltage U _N	300 V

cUL Recognized	
	B
Nominal current I _N	10 A
Nominal voltage U _N	300 V


EAC

cULus Recognized	
------------------	--

Drawings

Printed-circuit board connector - PST 1,0/12-H-3,5 - 1737116

Drilling diagram



Dimensioned drawing

