



fitted with

work equipment
connected load
system of protection
class of protection
usage
luminaire body
lamp cover
tubular sections
balance of articulation joints
weight (net)
mains lead

fastening

1 x halogen lamp QR-CBC51 20W/24° GU5.3 12V
 light colour warm white, 3000 K, Color Rendering Index (CRI)=98
 Energy efficiency category B
 electronic transformer
 230V; 50/60Hz
 IP 20
 II
 switch
 sectional aluminium, anodised, Jet black
 glass screen
 flexible metal tube, Jet black
 friction
 approx. 1.0 kg
 approx. 1.5 m; mains plug
 CEE 7/XVI
 screw-down flange, table base (accessory), table clamp (accessory), wall bracket (accessory)



CEE 7/XVI

illuminance

measuring conditions: d=50cm

Em: 2504 lx
E_{max}: 7375 lx
E_{min}: 182 lx

