





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		N1	REVISED PER ECO-11-004820	11MAR11	RK	HMR


- 1 CONTINUOUS STRIP ON REELS
- 2 ACCEPTS #18-#14 AWG WIRE SIZE
- 3 INSULATION RANGE IS .120-.170 DIA
- 4 MATING TAB THK IS .032±.001.
- 5 REELED WITH INTERLEAVING PAPER
- 6 PRELIMINARY - NOT FOR PRODUCTION



SECTION C-C




SECTION A-A



SECTION B-B

OBSOLETE	5 STANDARD	.000080 MIN TIN	6 1-63306-0
	REVERSE	-	63306-3
	STANDARD	.000080 MIN TIN	63306-2
	STANDARD	-	63306-1
	REELING	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 20JUN02		 TE Connectivity				
DIMENSIONS: INCHES		CHK P DESANTIS 20JUN02						
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD P DESANTIS 20JUN02		NAME RECEPTACLE, FASTON, .250 SERIES —			
	0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .010 4 PLC ± — ANGLES ± —		PRODUCT SPEC —					
	FINISH		APPLICATION SPEC —					
	MATERIAL 4M BRASS		WEIGHT —					
SEE TABLE		CUSTOMER DRAWING		SIZE A2	CAGE CODE 00779	DRAWING NO C-63306		RESTRICTED TO —
				SCALE 8:1		SHEET 1 of 1	REV N1	