






1. MATERIAL:
 - 1.1 HOUSING: UL94V-0; COLOR: SEE TABLE.
: NY9T, THERMOPLASTIC, HIGH TEMP.
: PBT, THERMOPLASTIC.
- 1.2 CONTACTS: PHOSPHOR BRONZE
- 1.3 SHELL: SPCC
- 1.4 BOARDLOCK: BRASS
- 1.5 RIVET: BRASS
2. FINISH:
 - 2.1 CONTACT:
GOLD PLATING ON CONTACT AREA,
100µ" MIN. MATTE TIN PLATING ON SOLDERTAIL,
50µ" MIN. NICKEL UNDERPLATED OVERALL.
 - 2.2 BOARDLOCK:
100µ" MIN. TIN PLATING
50µ" MIN. NICKEL UNDERPLATED OVERALL.
 - 2.3 SHELL: 50µ" MIN. NICKEL PLATING OVERALL.
 - 2.4 RIVET: NICKEL PLATING OVERALL.
3. RECOMMENDED PCB THICKNESS: 1.6mm
4. WAVE SOLDER CAPABLE TO 265°C
PER TE CONNECTIVITY SPEC. 109-202, CONDITION B.



RECOMMENDED P.C. BOARD LAYOUT



DETAIL Z
(W/SCREWLOCKS OPTION)

		300U BLUE	3.20	TRAY	10 	RIVET, THREADED W/O SCREW	5-1734344-3
OBSOLETE		300U BLUE	3.70	TRAY	30 	RIVET, THREADED W/O SCREW	2-1734344-4
		300U BLUE	3.20	TRAY	30 	RIVET, THREADED W/O SCREW	2-1734344-3
OBSOLETE		661C BLUE	2.67	TRAY	30 	RIVET, THREADED W/O SCREW	2-1734344-2
		661C BLUE	2.67	TRAY	G/F	W/FEMALE SCREWLOCKS (DETAIL Z)	1-1734344-2
		300U BLUE	3.20	TRAY	G/F	W/FEMALE SCREWLOCKS (DETAIL Z)	1-1734344-1
		BLACK	2.67	TUBE	15 	W/FEMALE SCREWLOCKS (DETAIL Z)	1734344-5
		300U BLUE	3.20	TUBE	10 	RIVET, THREADED W/O SCREW	1734344-4
OBSOLETE		300U BLUE	3.20	TRAY	10 	RIVET, THREADED W/O SCREW	1734344-3
		661C BLUE	2.67	TRAY	G/F	RIVET, THREADED W/O SCREW	1734344-2
		300U BLUE	3.20	TRAY	G/F	RIVET, THREADED W/O SCREW	1734344-1
	HSG RESIN	PANTONE COLOR	'L'	PACKAGING	GOLD PLATING	FASTENER OPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	16JAN2006
-----	-----------

J. LEE	
CHK	16JAN2006

S. HOU	12 JAN 2000
ATM	12 JAN 2000

APVD 16JAN2006
W.J. KE

PRODUCT SPEC	
--------------	--

108-57541

QUALIFICATION TEST REPORT

501-57623

WEIGHT	9.0g/PCS(W/ SCREW) 11.1g/PCS(W/O SCREW)
--------	--

CUSTOMER DRAWING

CUSTOMER DRAWING

TE Connectivity

6	NAME	RCPT ASM, SZ 1, 15 POSN, RT ANG, FRONT METAL, SHELL AMPLIMITE HD-22
---	------	---

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

SIZE	SIZE CODE	DRAWING NO.	RESTRICTED TO
A 7	00770	1774744	

A3	00779	G=1 / 34344	/-
----	-------	-------------	----

SCALE	SHEET	REV
1" = 10'	1 OF 3	B1

	/	=	of 5	D
--	---	---	------	---

1470-19 (3/11)

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

©

COPYRIGHT

BY

LOC

DIST


DW

REVISONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1.	-	-	-

NOTES:

- MATERIAL:
 - 1.1 TRAY: PVC
 - 1.2 SHIPPING CARTON: CORRUGATED FIBERBOARD
- DIMENSION:
 - 2.1 TRAY: L=320, W=230, H=18.9
 - 2.2 SHIPPING CARTON: L=361, W=245, H=272
- QUANTITY:
 - 3.1 PRIMARY PACKING: 100 PCS/TRAY
 - 3.2 SECONDARY PACKING: 10 TRAY/CARTON(1000PCS)
- CARTON WEIGHT:
 - 4.1 W/O SCREWLOCK
NET WEIGHT: 8.24 Kg
GROSS WEIGHT: 9.24 Kg
 - 4.2 WITH SCREWLOCK
NET WEIGHT: 10.24 Kg
GROSS WEIGHT: 11.24 Kg



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MMTOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±

FINISH

MATERIAL

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

STE TE Connectivity

NAME

RCPT ASM, SZ 1, 15 POSN,
RT ANG, FRONT METAL, SHELL
AMPLIMITE HD-22

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779




©=1734344

SCALE

SHEET

2 OF 3

REV B1



- NOTES:
- 1. MATERIAL:
 - 1.1 TRAY: PVC
 - 1.2 SHIPPING CARTON: CORRUGATED FIBERBOARD
 - 2. DIMENSION:
 - 2.1 TRAY: L=560, W=17.8, H=27.4
 - 2.2 SHIPPING CARTON: L=600, W=245, H=195
 - 3. QUANTITY:
 - 3.1 PRIMARY PACKING: 17 PCS/TUBE
 - 3.2 SECONDARY PACKING: 25 TUPE/BOX
 - 3.3 THIRD PACKING: 2 BOX/CARTON(850PCS)
 - 4. CARTON WEIGHT:
 - 4.1 W/O SCREWLOCK
 - NET WEIGHT: 8.24 Kg
 - GROSS WEIGHT: 9.24 Kg
 - 4.2 WITH SCREWLOCK
 - NET WEIGHT: 10 Kg
 - GROSS WEIGHT: 11 Kg

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CHK APVD		TE Connectivity	
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0 PLC ±		1 PLC ±		RCPT ASM, SZ 1, 15 POSN, RT ANG, FRONT METAL, SHELL AMPLIMITE HD-22	
2 PLC ±		3 PLC ±		SIZE	
4 PLC ±		ANGLES ±		CAGE CODE	
MATERIAL		FINISH		DRAWING NO	
				A300779C-1734344	
				RESTRICTED TO	
				SCALE	
				SHEET	
				3 OF 3	
				REV	
				B1	