






Electrical Specification:

DC resistance:

Primary: $63\Omega \pm 15\%$

Secondary: $63\Omega \pm 15\%$

Inductance, measured at 0.25V, series equivalent

200Hz >12H

4kHz > 1.8H

Leakage inductance (200Hz - 4kHz): 19mH nominal (35mH max.)

Harmonic distortion(dBm max.):

400Hz: -85

600Hz: -92


Return loss (200Hz - 4kHz) >20dB

Insertion loss @ 1kHz: 0.80dB nominal

Hi-pot, primary to secondary: 3.75kV min.

Storage temperature range: -25°C to +85°C

Do not pass DC through windings



Walters OEP Ltd.

Unit 5, Oxonian Park, Langford Locks,
Kidlington, Oxfordshire. OX5 1FP
Tel: (01865) 855085 Fax: (01865) 855075
Website: www.oep.co.uk

DESCRIPTION	ISSUE	DATE	DRAWN	CHECKED	DRAWING NUMBER
600Ω 56k line isolating transformer	1	15/02/00	CS		Z1656
	2	14/11/05	CS		
Scale : 2:1					
All dimensions in mm unless stated otherwise					