


**VentGLAND, SPRINT cable glands, metric, plastic**

**Protection class to EN 60 529:** IP 69k; IP 68 to 0,6 bar








**Temperature range:** -40°C to 100°C , intermittent up to approx. 120°C

**Material:**

- Cable gland: polyamide
- Gasket: EPDM
- Membrane: ePTFE

**Equipment:**

- A micro-porous, liquid-tight and breathable ePTFE membrane as an integrated element of cable gland
- Maximum traction relief through WISKA patent lamella
- Seal-tight to enclosure rack through additional EPDM sealing ring
- Same sealing range on all SPRINT-glands
- Also available with reduction insert, multiple sealing insert, special sealing insert and dust-protection gasket

Type	WISKA-No. RAL 7035 	WISKA-No. RAL 9005 		 mm	 mm	 mm	 SW mm	E1 mm	TL mm
ESVG 20	10060974	10060802	1	M 20x1,5	10	6 - 13	24	27	41
ESVG 25	10100666	10100667	1	M 25x1,5	10	9 - 17	29	32	45
ESVG 32	10100801	10100802	1	M 32x1,5	12	13 - 21	36	40	49

© 2010 WISKA Hoppmann & Mulsow GmbH

Kisdorfer Weg 28

D-24568 Kaltenkirchen

Phone: +49 (0)4191 / 508-100

Fax: +49 (0)4191 / 508-209