



FACE VIEW - MALE INSERT SCALE 2 : 1

1 WHITE 2 BLACK	1 GREEN/YELLOW 2 BLACK 3 WHITE	1 BLACK 2 WHITE 3 RED 4 GREEN/YELLOW	1 WHITE 2 RED 3 GREEN/YELLOW 4 ORANGE 5 BLACK	1 WHITE 2 RED 3 GREEN/YELLOW 4 ORANGE 5 BLACK 6 BLUE



MALE INSERT - FRONT VIEW



SECTION Z-Z

FINAL ASSEMBLY
1300130076

ENTER DESCRIPTION EC NO: WNA2010-0057 DRAWN BY: NKUMAR01 2009/07/31 CHKD: JFMURPHY APPR: JFMURPHY 2009/08/10 REV A	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY NKUMAR01	DATE 31/07/09	TITLE MC 2P MR 12IN. 16/1 PVC				
			4 PLACES	± ---	± ---	CHECKED BY BWOODMAN	DATE 31/07/09					
			3 PLACES	± ---	± ---	APPROVED BY JFMURPHY		DATE 31/07/09	MOLEX MOLEX INCORPORATED			
			2 PLACES	± ---	± ---							
			1 PLACE	± ---	± ---	MATERIAL NO. 9999999999		DOCUMENT NO. SD-130013-076	SHEET NO. 1 OF 2			
			ANGULAR ±1/2°			SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									

J

I

H

G

F

E

D

C

B

A

J

I

H

G

F

E

D

C

B

A

MALE RECEPTACLE ASSEMBLY				
2 POLE	3 POLE	4 POLE	5 POLE	6 POLE
QUANTITY				
1	1	1	1	1
2	3	4	5	6
1	1	1	1	1
1				
	1			
		1		
			1	
				1
1	1	1	1	1
				1
	1	1	1	1
			1	1
		1	1	1
1	1	1	1	1

Sl. No.	DESCRIPTION	MATERIAL	FINISH
1	RECEPTACLE SHELL	ZINC DIECAST	BLACK E-COAT
2	PIN CONTACT 16AWG	COPPER ALLOY	GOLD PLATED
3	LABEL	PLASTIC FILM	BLACK/YELLOW
4	2P MALE INSERT PVC A SIZE	PVC	YELLOW
	3P MALE INSERT PVC A SIZE	PVC	YELLOW
	4P MALE INSERT PVC A SIZE	PVC	YELLOW
	5P MALE INSERT PVC A SIZE	PVC	YELLOW
	6P MALE INSERT PVC A SIZE	PVC	YELLOW
5	#16-1 WHT PVC WIRE UL1015	PVC JACKET	WHITE
	#16-1 RED PVC WIRE UL1015	PVC JACKET	RED
	#16-1 ORN PVC WIRE UL1015	PVC JACKET	ORANGE
	#16-1 GRN/YEL PVC WIRE UL1015	PVC JACKET	GREEN/YELLOW
	#16-1 BLU PVC WIRE UL1015	PVC JACKET	BLUE
	#16-1 BLK PVC WIRE UL1015	PVC JACKET	BLACK

POLE COUNT	MAX. VOLTAGE RATING	MAX. CURRENT RATING
2 POLE	600 VOLTS	13 AMPS
3 POLE	600 VOLTS	13 AMPS
4 POLE	600 VOLTS	10 AMPS
5 POLE	600 VOLTS	8 AMPS
6 POLE	600 VOLTS	8 AMPS

PART NUMBER	DESCRIPTION	FINISHED LENGTH
1300130076	1R2006A20A120	12.0" +.75" -0 [0.3M +19.1MM -0]
1300130084	1R2006A20F060	6.0' +2.19" -0 [1.8M +55.6MM -0]
1300130202	1R3006A20A120	12.0" +.75" -0 [0.3M +19.1MM -0]
1300130215	1R3006A20F060	6.0' +2.19" -0 [1.8M +55.6MM -0]
1300130353	1R4006A20A120	12.0" +.75" -0 [0.3M +19.1MM -0]
1300130361	1R4006A20F060	6.0' +2.19" -0 [1.8M +55.6MM -0]
1300130493	1R5006A20A120	12.0" +.75" -0 [0.3M +19.1MM -0]
1300130503	1R5006A20F060	6.0' +2.19" -0 [1.8M +55.6MM -0]
1300130593	1R6006A20A120	12.0" +.75" -0 [0.3M +19.1MM -0]
1300130605	1R6006A20F060	6.0' +2.19" -0 [1.8M +55.6MM -0]

ENTER DESCRIPTION
EC NO: WNA2010-0057
DRAWN BY: NKUMAR01 2009/07/31
CHKD: JFMURPHY
APPR: JFMURPHY 2009/08/10

DESCRIPTION
REV

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± ---
2 PLACES ± --- ± ---
1 PLACE ± --- ± ---
ANGULAR ±1/2°
DRAFT WHERE APPLICABLE
MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM
DRAWN BY: NKUMAR01
CHECKED BY: BWOODMAN
APPROVED BY: JFMURPHY
DATE: 31/07/09
DATE: 31/07/09
DATE: 31/07/09

SCALE
2:1
TITLE
MC 2P MR 12IN.
16/1 PVC

MOLEX INCORPORATED

DOCUMENT NO. SD-130013-076
SHEET NO. 2 OF 2

tb_frame_C_P_AM_T
Rev. E 2006/04/15

121110987654321