


Pos	Dim.A	Dim.B	Dim.C	Pos	Dim.A	Dim.B	Dim.C
4	9.70	3.81	5.60	16	24.94	19.05	20.84
6	12.24	6.35	8.14	18	27.48	21.59	23.38
8	14.78	8.89	10.68	20	30.02	24.13	25.92
10	17.32	11.43	13.22	22	32.56	26.67	28.46
12	19.86	13.97	15.76	24	35.10	29.21	31.00
14	22.40	16.51	18.30	26	37.64	31.75	33.54

Specifications:

Current rating:1.5A AC,DC
Voltage rating:230V AC, DC
Contact tesistance:20m ohm Max
Insulation resistance:1000M ohm Min
Withstanding voltage:AC 500V AC/minute
Operating Temperature:-40°C ~ +105°C
Materials:
Insulator:High Temp Plastic (UL94V-0)
Contact material:Phosphor Bronze
Finish:Tin Plated

How to Order


TMM-X-X-XX-X

Type
1-IDC Male
2-IDC Plug
3-DIP Male Straight
4-DIP Female Straight
5-DIP Female R/A
6-SMT Female Straight

Locking System
0-without lock
L-with lock

Packaging
1 - Tape & Reel with vacuum cap
2 - Tube
3 - Bag
4-Tape&Reel without vacuum cap

Number of Positions
04, 06, 08, 10, 12, 14,
16, 18, 20, 22, 24 or 26



PCB Layout



TOLERANCE (mm)	APPROVALS	DATE	TITLE	AMPHENOL
X. ±0.3	DRAWN Stephane	2009/10/07	TMM Series	Amphenol European Design Center
X.X ±0.2	CHECKED Rob	2009/10/07	R/A Dip Female w/Lock	Scale N.A. Sheet 1 of 1
X.XX ±0.15	APPROVED Rob	2009/10/07		
UNLESS OTHERWISE SPECIFIED	UNIT: mm	SIZE: A4	DRAWING N° TMM-5-L-XX-X	REV. E