





A

B


C

D

E



ZONA A SALDARE SU C.S.  
(SOLDER AREA)



AREA DI CONTATTO  
(CONTACT AREA)

SEZ. PARZIALE (PARTIAL SEC.) A-A

|      |       |                           |                           |                           |          |
|------|-------|---------------------------|---------------------------|---------------------------|----------|
| 58.5 | 53.34 | 280376-3                  | <del>280376-2</del> 6     | 280376-1                  | 22       |
| 40.7 | 35.56 | 280375-3                  | 280375-2                  | 280375-1                  | 15       |
| 33.1 | 27.94 | 280520-3                  | 280520-2                  | 280520-1                  | 12       |
| 28.0 | 22.86 | 280374-3                  | 280374-2                  | 280374-1                  | 10       |
| 25.4 | 20.32 | <del>280508-3</del> 5     | 280508-2                  | 280508-1                  | 9        |
| 22.9 | 17.78 | <del>280373-3</del> 6     | 280373-2                  | 280373-1                  | 8        |
| 17.8 | 12.70 | 280372-3                  | 280372-2                  | 280372-1                  | 6        |
| 12.7 | 7.62  | 280371-3                  | 280371-2                  | 280371-1                  | 4        |
| 7.7  | 2.54  | 280370-3                  | 280370-2                  | 280370-1                  | 2        |
| D    | B     | NUMERO<br>(PART NUMBER) 3 | NUMERO<br>(PART NUMBER) 2 | NUMERO<br>(PART NUMBER) 1 | NO. POS. |

- 1 FINITURA (FINISH): STAGNATO 3.5µm (TIN PLATED 3.5µm).
- 2 FINITURA (FINISH): DORATO 0.4µm NELL'AREA DI CONTATTO E STAGNATO 2.5µm NELLA ZONA A SALDARE, SU 1.3µm DI NI. (DUPLEX PLATED 0.4µm GOLD IN CONTACT AREA AND 2.5µm TIN IN SOLDER AREA, OVER 1.3µm NICKEL).
- 3 FINITURA (FINISH): DORATO 0.8µm NELL'AREA DI CONTATTO E STAGNATO 2.5µm NELLA ZONA A SALDARE, SU 1.3µm DI NI. (DUPLEX PLATED 0.8µm GOLD IN CONTACT AREA AND 2.5µm TIN IN SOLDER AREA, OVER 1.3µm NICKEL).
- 4 MATERIALI (MATERIALS):  
-BLOCCHETTI: POLIESTERE AUTOESTINGUENTE UL94V-0, COLORE NERO.  
(HOUSINGS: FLAME RETARDANT THERMOPLASTIC, COLOR BLACK).  
-CONTATTI STAGNATI: BRONZO FOSFOROSO.  
(TIN PLATED CONTACTS: PHOSPHOR BRONZE).  
-CONTATTI DORATI: OTTONE.  
(GOLD PLATED CONTACTS: BRASS).

5 P/N OBSOLETO (OBSOLETE P/N)

6 OBSOLETE

CUSTOMER DRAWING FOR REFERENCE ONLY  
DISEGNO PER CLIENTE SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED  
© COPYRIGHT 19 BY TE INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. TE PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING

TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO  
(TOLERANCES, UNLESS OTHERWISE SPECIFIED)  
± 0.3

ANGOLI (ANGLES) ± 2°  
MATERIALI (MATERIALS)  
VEDERE NOTA (SEE NOTE) 4  
TE Connectivity

|     |                                              |                        |           |                |                                             |
|-----|----------------------------------------------|------------------------|-----------|----------------|---------------------------------------------|
| L2  | ECR-10-022530                                | KK                     | 10 FEB 90 | DIS. G. CAMPIA | DESCRIZIONE (DESCRIPTION) AMPMODU II HEADER |
| L1  | MODIFIED PER ET00-0263-99                    | 10 FEB 90              | 28-9      | 12 FEB 90      | ASS. IES, STRAIGHT, SINGLE ROW              |
| L   | OBSOLETE P/N 280503-3 (ET00-518-96)          | C.P.                   | 4-12 '96  | CONT. - (CHK)  |                                             |
| K   | AGGIORNATO E RIDISEGNATO (REVISED & REDRAWN) | G.C.                   | 2/90      | APP. - (APP.)  |                                             |
| REV | REVISIONI (REVISION RECORD)                  | DIS. DATA (COR) (DATE) |           |                |                                             |

LOC. SIZE NUMERO (CONG NO) REV. FOGLIO (SHEET) 1 A3 C-280370 L2 1 DI (OF) 1