

LOC		DIST		REVISIONS			
AJ		16		P	LTR	DESCRIPTION	DATE
							DWN
							APVD
				0		REV PER EC-0S14-0496-04	01FEB2005
							LV
							KW

- 1

PHOSPHOR BRONZE PER QQ-B-750
- 2

ZINC PER QQ-Z-363.
- 3


PTFE PER MIL-P-19468.
- 4

TIN PLATE PER ASTM B 545.
3.81μm [.000150] MINIMUM THICK.
- 5


CONNECTOR WILL ACCEPT A CENTER CONDUCTOR
DIAMETER OF 0.56[.022]–1.19[.047].
- 6

RETURN LOSS: –20 dB NOMINAL, UP TO 1 GHz.
- 7



MAJOR DIAMETER MODIFIED TO .363 REF.



SUGGESTED PANEL CUTOUT



RECOMMENDED PCB CONFIGURATION



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA – 01FEB2005	5887046-1	
DIMENSIONS: mm [INCHES]		CHK J. HAVENER 01FEB2005	PART NUMBER	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K. WEIDNER 01FEB2005	NAME	
0 PLC ± -		PRODUCT SPEC	JACK, PCB, VERTICAL, F SERIES	
1 PLC ± -		APPLICATION SPEC	SIZE	
2 PLC ± -		WEIGHT	CAGE CODE	
3 PLC ± 0.20 [.008]		CUSTOMER DRAWING	DRAWING NO	
4 PLC ± -		SCALE 5:1	SHEET 1 OF 1	
ANGLES ± -		REV 0		
FINISH				
SEE NOTES 1-3				
SEE NOTE 4				