



### Pneumatic Tensioning Tool with Plastic Housing

- MK7P up to 4.8 mm strap width

The MK7P pneumatic bundling tool sets a new benchmark for the rational application of ties in the industrial production process. Improved compressed air supply moves the tensioning piston faster than in comparable tools.

#### Features and Benefits

- Pneumatic tensioning tool
- Light glass-fibre-reinforced housing
- For cable ties up to 4.8 mm width
- For consistent tensioning and automatically flush cutting
- Infinitely adjustable tension force
- High application speed



MK7P.



The easy to use quick-set-knob.

<b>Air Supply</b>	Non oiled / oiled
<b>Air Pressure (min.)</b>	3 Bar
<b>Air Pressure (max.)</b>	6 Bar
<b>Hose Internal Diameter</b>	4.0 mm
<b>L x H x W</b>	approx. 220 x 170 x 40 mm
<b>Specifications</b>	CE, GS

**RoHS** ✓

TYPE	Strap Width max. (G)	Strap Thickness max.	Weight	Article-No.
MK7P	4.8	1.5	0.43 kg	110-07100
Compressed-air hose	-	-	0.35 kg	110-30002
Replacement Blade	-	-	0.01 kg	110-07111
Lock cap tensioning knob	-	-	0.011 kg	110-07200

All dimensions in mm. Subject to technical changes.



Please note! Not all products listed on this page may have this approval. For product specific approvals please refer to the Appendix.