

[Return to](#) | [XBee® ZB](#)

Programmable XBee-PRO ZB extended module w/ integrated wire an



Part Numbers:

North America: **XBP24BZ7WITB003**

International: **XBP24BZ7WITB003J**

Related Accessories/Models

AC Power Supplies

AC Power Supply - 9VDC, 120-240VAC, 1.1A, non-locking barrel (US & Japan only).

[View Details](#)



AC Power Supply - 12VDC, 120-240VAC, 1.5A, wall mount, non-locking barrel (ACC-PK1 plug kit required for international).

[View Details](#)

AC Plug Kit - EU, UK, AU. Compatibility: XA-ACC-PS, XA-ACC-PS5-NR

[View Details](#)

DC Power Cords

DC Power Cord - 2.1mm/5mm, non-locking barrel plug to clipped ends, 6'.

[View Details](#)

DC Power Cord - 2.1mm/5mm, non-locking barrel plug to 9V battery clip.

[View Details](#)

Miscellaneous Accessories

Loopback Plug - DB9 male and DB9 female

[View Details](#)

Cable Adapter - DB9 female to DB9 female, null modem

[View Details](#)

Loopback Plug - DB9 female

[View Details](#)

Interface Board - XBee, RS232

[View Details](#)

Interface Board - XBee, RS232, development

[View Details](#)

Interface Board - XBee, USB


[View Details](#)

Interface Board - XBee, USB, development

[View Details](#)

Debugger - Freescale, HCS08, HCS12, RS08

[View Details](#)



Building Wireless Sensor Networks: with ZigBee, XBee, Arduino, and Processing
Rob Faludi

[View Details](#)

Cables

Cable - USB-A male to USB-B male, 6'.

[View Details](#)

Cable - DB9 male to DB9 female, straight-through, 6'.

[View Details](#)

Your M2M Expert[®] for **Business** for **Developers**

Digi

[Products](#)

[Services](#)

[Device Cloud](#)

[Industries](#)

[Support](#)

[Learning Center](#)

[Digi Blog](#)

[News](#)

[Events](#)

[Videos](#)

[Security](#)

[How to Buy](#)

[Export Compliance](#)

[Careers](#)

[Site Map](#)

[About Us](#)

[Customer Successes](#)

[Government](#)

[Partner Login](#)

[Investor Relations](#)

C

[PI](#)

[Ei](#)

[C](#)

[Fr](#)

Copyright © 1996-2014 Digi International Inc. All rights reserved. [Legal](#)