



Main

Relay application	Remote control
Range of product	DuoLine
Device short name	TL'clic
Poles description	1P
Pole contact composition	1 NO
[In] rated current	16 A
Network type	AC
Network frequency	50/60 Hz
Control circuit voltage	230 V AC 50/60 Hz
Supply inrush power	19 VA
9 mm pitches	2

Complementary

[Ue] rated operational voltage	250 V AC 50/60 Hz
Control type	Remote control Toggle
Control signal type	Impulse
Switching frequency	5 switching operation/minute
Impulse duration	50 ms
Remote control type	Illuminated pushbutton 3 mA
Local signalling	ON/OFF indication
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Comb busbar distribution block compatibility	Upside: Bar'clic
Height	60 mm
Width	18 mm
Depth	84 mm
Connections - terminals	Prefabricated connection Tunnel type terminals 2 cable(s) 1.5 mm ² rigid Tunnel type terminals 2 cable(s) 1.5 mm ² flexible with Tunnel type terminals 2 cable(s) 1.5 mm ² flexible without Tunnel type terminals 1 cable(s) 4 mm ² flexible without
Auxiliary connection terminal	Control circuit: tunnel type terminals 2 cable(s) rigid 0.5...1.5 mm ² Control circuit: tunnel type terminals 2 cable(s) flexible 0.5...1.5 mm ² with cable end Control circuit: tunnel type terminals 2 cable(s) flexible 0.5...1.5 mm ² without cable end

Environment

Product certifications	NF
RoHS EUR conformity date	0633
RoHS EUR status	Compliant