

Base strip - CIOC 3-4-FV - 1701552

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Header, Nominal current: 3 A, Rated voltage (III/2): 32 V, Number of positions: 12, Pitch: 2 mm, Color: black, Contact surface: Gold, Mounting: Soldering

The illustration shows the 4-pos. version

Why buy this product

- 3 and 4-pos. miniature headers for CIOC ...-M plugs
- Gold-plated contact system
- Enables the space-saving design of I/O modules and signal distributors

Key commercial data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 543521
Weight per Piece (excluding packing)	22.22 g
Custom tariff number	85366990
Country of origin	Japan
Note	Made to Order (non-returnable)

Technical data

Dimensions

Pitch	2 mm
Dimension a	4 mm
Pin spacing	2.00 mm

General

Range of articles	CIOC-FV
Rated voltage (III/2)	32 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	3 A
Maximum load current	3 A
Insulating material	PA
Inflammability class according to UL 94	V0

Base strip - CIOC 3-4-FV - 1701552

Technical data

General

Color	black
Number of positions	12

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440309

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

Base strip - CIOC 3-4-FV - 1701552

Approvals

UL Recognized	
Nominal current IN	3 A
Nominal voltage UN	32 V


cUL Recognized	
Nominal current IN	3 A
Nominal voltage UN	32 V

EAC

cULus Recognized

Drawings

Drilling diagram



Dimensioned drawing

