


Capacitor, Ceramic, 0.1 uF, +/-10% Tol, 50 V, X8L



General Information	
Supplier:	KEMET
Application:	General Purpose
Sub Application:	AEC-Q200
Temperature Coefficient:	X8L
Body Type:	Axial Conformal
Lead Type:	Wire Leads
Termination Type:	Tin (Sn)
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
D	2.31	MAX
L	4.32	MAX
LL	25.4	MIN
F	0.51	+0.025/-0.076

Specifications	
Capacitance:	0.1 uF
Voltage:	50 V
Tolerance:	+/-10%
Temperature Range:	-55/+150C
Dissipation Factor:	2.5%
Insulation Resistance:	10 GOhm

Packaging Specifications	
Package Kind:	T&R
Package Size:	12in
Package Type:	Paper
Package Quantity:	5000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.