

Fuse modular terminal block - USED 27 N - 3048373

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Fuse terminal blocks for DIAZED fuse inserts

Why buy this product

- ✓ The major advantage of the DIAZED® system is its dielectric strength of up to 500 V
- ✓ Conductor cross sections of up to 35 mm² can be connected with the user-friendly spring-cage connection
- ✓ Original DIAZED®-E 27 threads are used in closed housing
- ✓ This fuse terminal block accommodates DIAZED® fuses



Key commercial data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 976286
Weight per Piece (excluding packing)	181.64 g
Custom tariff number	85363030
Country of origin	Germany

Technical data

General

Number of levels	1
Number of connections	2
Color	light gray
Insulating material	Duroplast
Inflammability class according to UL 94	V0
Fuse	D II / E 27
Fuse type	Screw cartridge
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III

Fuse modular terminal block - USED 27 N - 3048373

Technical data

General

Insulating material group	IIIb
Current	25 A
Additional text	with 35 mm ² conductor cross section
Nominal current I _N	25 A (the current is determined by the fuse used)
Nominal voltage U _N	500 V (the voltage is determined by the fuse used)
Open side panel	nein
Shock protection test specification	DIN EN 50274 (VDE 0660-514):2002-11
Back of the hand protection	guaranteed
Finger protection	guaranteed
Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))	165 °C

Dimensions

Width	40 mm
Length	80 mm
Height NS 35/7,5	62.5 mm
Height NS 35/15	70 mm

Connection data

Conductor cross section solid min.	1.5 mm ²
Conductor cross section solid max.	35 mm ²
Conductor cross section stranded min.	1.5 mm ²
Conductor cross section stranded max.	35 mm ²
Conductor cross section AWG/kcmil min.	16
Conductor cross section AWG/kcmil max	2
Conductor cross section stranded, with ferrule without plastic sleeve min.	1.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	25 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	1.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	25 mm ²
Cross section with insertion bridge, solid max.	25 mm ²
Cross section with insertion bridge, stranded max.	25 mm ²
2 conductors with same cross section, solid min.	1.5 mm ²
2 conductors with same cross section, solid max.	10 mm ²
2 conductors with same cross section, stranded min.	1.5 mm ²
2 conductors with same cross section, stranded max.	10 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	1.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	10 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	1.5 mm ²

Fuse modular terminal block - USED 27 N - 3048373

Technical data

Connection data

2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	10 mm ²
Cross section with insertion bridge, solid max.	25 mm ²
Cross section with insertion bridge, stranded max.	25 mm ²
Connection method	Screw connection
Stripping length	19 mm
Internal cylindrical gage	B8
Screw thread	M6
Tightening torque, min	3.5 Nm
Tightening torque max	4 Nm

Classifications

eCl@ss

eCl@ss 4.0	27141116
eCl@ss 4.1	27141116
eCl@ss 5.0	27141116
eCl@ss 5.1	27141116
eCl@ss 6.0	27141116
eCl@ss 7.0	27141116

ETIM

ETIM 2.0	EC000899
ETIM 3.0	EC000899
ETIM 4.0	EC000899
ETIM 5.0	EC000899

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121411
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

GL / RS / EAC

Fuse modular terminal block - USED 27 N - 3048373

Approvals

Ex Approvals

Approvals submitted

Approval details

GL

RS

EAC

Accessories

Accessories

Fuse

Fuse insert - S-II- 2 A/500 V - 0913605



Fuse insert, Nominal current: 2 A, Length: 10 mm, Width: 10 mm, Color: pink

Fuse insert - S-II- 4 A/500 V - 0913618



Fuse insert, Nominal current: 4 A, Length: 10 mm, Width: 10 mm, Color: brown

Fuse insert - S-II- 6 A/500 V - 0913621



Fuse insert, Nominal current: 6 A, Length: 10 mm, Width: 10 mm, Color: green

Fuse modular terminal block - USED 27 N - 3048373

Accessories

Fuse insert - S-II-10 A/500 V - 0913634



Fuse insert, Nominal current: 10 A, Length: 10 mm, Width: 10 mm, Color: red

Fuse insert - S-II-16 A/500 V - 0913647



Fuse insert, Nominal current: 16 A, Length: 10 mm, Width: 10 mm, Color: gray

Fuse insert - S-II-20 A/500 V - 0913650



Fuse insert, Nominal current: 20 A, Length: 10 mm, Width: 10 mm, Color: blue

Fuse insert - S-II-25 A/500 V - 0913663



Fuse insert, Nominal current: 25 A, Length: 10 mm, Width: 10 mm, Color: yellow

Marker carriers

Marker carriers - MA 20X 8 BK - 0814270



Marker carrier, for SS-ZB contactor marking Zack marker strip

Mounting rail

Fuse modular terminal block - USED 27 N - 3048373

Accessories

DIN rail perforated - NS 35/ 7,5 PERF 2000MM - 0801733



DIN rail, material: steel galvanized and passivated with a thick layer, perforated, height 7.5 mm, width 35 mm, length: 2000 mm

DIN rail, unperforated - NS 35/ 7,5 UNPERF 2000MM - 0801681



DIN rail, material: Steel, unperforated, height 7.5 mm, width 35 mm, length: 2 m

DIN rail perforated - NS 35/ 7,5 WH PERF 2000MM - 1204119



DIN rail 35 mm (NS 35)

DIN rail - NS 35/ 7,5 WH UNPERF 2000MM - 1204122



DIN rail 35 mm (NS 35)

DIN rail, unperforated - NS 35/ 7,5 AL UNPERF 2000MM - 0801704



DIN rail, unperforated, Width: 35 mm, Height: 7.5 mm, Length: 2000 mm, Color: silver

Fuse modular terminal block - USED 27 N - 3048373

Accessories

DIN rail perforated - NS 35/ 7,5 ZN PERF 2000MM - 1206421



DIN rail, material: Galvanized, perforated, height 7.5 mm, width 35 mm, length: 2 m

DIN rail, unperforated - NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



DIN rail, material: Galvanized, unperforated, height 7.5 mm, width 35 mm, length: 2 m

DIN rail, unperforated - NS 35/ 7,5 CU UNPERF 2000MM - 0801762



DIN rail, material: Copper, unperforated, height 7.5 mm, width 35 mm, length: 2 m

End cap - NS 35/ 7,5 CAP - 1206560



DIN rail end piece, for DIN rail NS 35/7.5

Screwdriver tools

Screwdriver - SZF 3-1,0X5,5 - 1206612



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 1.0 x 5.5 x 150 mm, 2-component grip, with non-slip grip

Drawings

Fuse modular terminal block - USED 27 N - 3048373

Circuit diagram



Phoenix Contact 2015 © - all rights reserved
<http://www.phoenixcontact.com>