

Ordering number FP11077_LISA2-WW-CLIP

Family	Lisa2	FWHM	(simulated)
Type	Assembly	Efficiency	(simulated) 0 %
LED	Double Dome (GM2BB)	cd/Im	-
Color	Black	Gerber File	Available
Diameter	9.9 mm		
Height	7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Clips, glue		
Status	Ready		

Ordering number FP11431_LISA2-WWW-CLIP

Family	Lisa2	FWHM	(simulated) 70
Type	Assembly	Efficiency	(simulated) 0 %
LED	Double Dome (GM2BB)	cd/Im	-
Color	Black	Gerber File	Available
Diameter	9.9 mm		
Height	7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Clips, glue		
Status	Ready		

Ordering number FP11856_LISA2-O-90-CLIP

Family	Lisa2	FWHM	(simulated) 48+20
Type	Assembly	Efficiency	(simulated) 0 %
LED	Double Dome (GM2BB)	cd/Im	-
Color	Black	Gerber File	Available
Diameter	9.9 mm		
Height	6.8 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Clips, glue		
Status	Ready		

Ordering number FP11121_LISA2-O-CLIP

Family	Lisa2	FWHM	10+32 degrees
Type	Assembly	Efficiency	(simulated) 0 %
LED	Double Dome (GM2BB)	cd/Im	-
Color	Black	Gerber File	Available
Diameter	9.9 mm		
Height	6.8 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Clips, glue		
Status	Ready		

**Ordering number FP11085_LISA2-RS-CLIP**

Family	Lisa2	FWHM	18 degrees
Type	Assembly	Efficiency	(simulated) 0 %
LED	Double Dome (GM2BB)	cd/Im	-
Color	Black	Gerber File	Available
Diameter	9.9 mm		
Height	6.8 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Clips, glue		
Status	Ready		

Ordering number FP11075_LISA2-M-CLIP

Family	Lisa2	FWHM	28 degrees
Type	Assembly	Efficiency	(simulated) 0 %
LED	Double Dome (GM2BB)	cd/Im	-
Color	Black	Gerber File	Available
Diameter	9.9 mm		
Height	6.8 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Clips, glue		
Status	Ready		

Ordering number FP11076_LISA2-W-CLIP

Family	Lisa2	FWHM	44 degrees
Type	Assembly	Efficiency	(simulated) 0 %
LED	Double Dome (GM2BB)	cd/Im	-
Color	Black	Gerber File	Available
Diameter	9.9 mm		
Height	6.8 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Clips, glue		
Status	Ready		

NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.



PRODUCT DATASHEET

Lisa2 series

last update 3/5/2012

SHARP

GENERAL INFORMATION

- Product series especially designed & optimized for Double Dome (GM2BB) series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.

Please find more information about used material from below:

http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20UL94_Yellow%20Card.pdf

<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20PLEXIGLAS-Datasheet.pdf>

- Optic holder molded by high quality PC material (120 degrees of Celcius / 248 degrees of Fahrenheit).

D C B A

4

3

2


1

4


3

2

1




Detail A
Scale: 8:1



Bottom view
Scale: 4:1

Lens

Holder



Front view
Scale: 4:1

Materials:
Lens PMMA
Holder PC

This drawing is our property.
It can't be reproduced
or communicated without
our written agreement.



L
T
F
F

e
e
l
i
n

N

d

DRAWING TITLE

Datasheet Lisa2-clip16-XP series Assy

DRAWN BY

DATE

20.7.2011

CHECKED BY

DATE

20.7.2011

DESIGNED BY

DATE

19.10.2009

SIZE

A4

DRAWING NUMBER

REV

2

SCALE

4:1

WEIGHT (g)

SHEET

1/1

D

A