

Information Sheet

SECTION 1. Identification of the substance/mixture and of the company/undertaking.

1.1. Product identifier.

Code. **HI7020**
Product name. **200 to 275 mV ORP Test Solution**

1.2. Relevant identified uses of the substance or mixture and uses advised against.

Intended use. **Test Solution for Platinum and Gold ORP Electrodes.**

1.3. Details of the supplier of the safety data sheet.

Name. **Hanna Instruments S.R.L.**
Full address. **str. Hanna Nr 1**
District and Country. **457260 loc. Nusfalau (Salaj)**
Romania
Tel. **(+40) 260607700**
Fax. **(+40) 260607700**

e-mail address of the competent person.
responsible for the Safety Data Sheet.

msds@hanna.ro

1.4. Emergency telephone number.

For urgent inquiries refer to. **Emergency Number - International: +(1)-703-527-3887 - UK, London:
+(44)-870-8200418 - CHEMTREC 24 hours/365 days**

SECTION 2. Hazards identification.

2.1. Classification of the substance or mixture.

The product is not classified as hazardous pursuant to the provisions set forth in EC Regulation 1272/2008 (CLP) (and subsequent amendments and supplements).

Hazard classification and indication: --

2.2. Label elements.

Hazard pictograms: --

Signal words: --

Hazard statements: --

Precautionary statements: --

2.3. Other hazards.

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

SECTION 3. Composition/information on ingredients.

3.1. Substances.

Information not relevant.

3.2. Mixtures.

The product does not contain substances classified as being hazardous to human health or the environment pursuant to the provisions Regulation (EU) 1272/2008 (CLP) (and subsequent amendments and supplements) in such quantities as to require the statement.

SECTION 4. First aid measures.

4.1. Description of first aid measures.

Not specifically necessary. Observance of good industrial hygiene is recommended.

4.2. Most important symptoms and effects, both acute and delayed.

No episodes of damage to health ascribable to the product have been reported.

4.3. Indication of any immediate medical attention and special treatment needed.

Information not available.

SECTION 5. Firefighting measures.

5.1. Extinguishing media.

SUITABLE EXTINGUISHING EQUIPMENT

The extinguishing equipment should be of the conventional kind: carbon dioxide, foam, powder and water spray.

UNSUITABLE EXTINGUISHING EQUIPMENT

None in particular.

5.2. Special hazards arising from the substance or mixture.

HAZARDS CAUSED BY EXPOSURE IN THE EVENT OF FIRE

Do not breathe combustion products.

5.3. Advice for firefighters.

GENERAL INFORMATION

Use jets of water to cool the containers to prevent product decomposition and the development of substances potentially hazardous for health. Always wear full fire prevention gear. Collect extinguishing water to prevent it from draining into the sewer system. Dispose of contaminated water used for extinction and the remains of the fire according to applicable regulations.

SPECIAL PROTECTIVE EQUIPMENT FOR FIRE-FIGHTERS

Normal fire fighting clothing i.e. fire kit (BS EN 469), gloves (BS EN 659) and boots (HO specification A29 and A30) in combination with self-contained open circuit positive pressure compressed air breathing apparatus (BS EN 137).

SECTION 6. Accidental release measures.

6.1. Personal precautions, protective equipment and emergency procedures.

Block the leakage if there is no hazard.

Wear suitable protective equipment (including personal protective equipment referred to under Section 8 of the safety data sheet) to prevent any contamination of skin, eyes and personal clothing. These indications apply for both processing staff and those involved in emergency procedures.

6.2. Environmental precautions.

The product must not penetrate into the sewer system or come into contact with surface water or ground water.

6.3. Methods and material for containment and cleaning up.

Collect the leaked product into a suitable container. If the product is flammable, use explosion-proof equipment. Evaluate the compatibility of the container to be used, by checking section 10. Absorb the remainder with inert absorbent material.

Make sure the leakage site is well aired. Contaminated material should be disposed of in compliance with the provisions set forth in point 13.

6.4. Reference to other sections.

Any information on personal protection and disposal is given in sections 8 and 13.

SECTION 7. Handling and storage.

7.1. Precautions for safe handling.

Before handling the product, consult all the other sections of this material safety data sheet. Avoid leakage of the product into the environment. Do not eat, drink or smoke during use.

7.2. Conditions for safe storage, including any incompatibilities.

Keep the product in clearly labelled containers. Keep containers away from any incompatible materials, see section 10 for details.

SECTION 7. Handling and storage. ... / >>**7.3. Specific end use(s).**

Information not available.

SECTION 8. Exposure controls/personal protection.**8.1. Control parameters.****RESPIRATORY PROTECTION**

None required, unless indicated otherwise in the chemical risk assessment.

Information not available.

8.2. Exposure controls.

Comply with the safety measures usually applied when handling chemical substances.

HAND PROTECTION

None required.

SKIN PROTECTION

None required.

EYE PROTECTION

None required.

RESPIRATORY PROTECTION

None required, unless indicated otherwise in the chemical risk assessment.

ENVIRONMENTAL EXPOSURE CONTROLS.

The emissions generated by manufacturing processes, including those generated by ventilation equipment, should be checked to ensure compliance with environmental standards.

SECTION 9. Physical and chemical properties.**9.1. Information on basic physical and chemical properties.**

Appearance	liquid
Colour	brown
Odour	pungent
Odour threshold.	Not available.
pH.	4,3
Melting point / freezing point.	Not available.
Initial boiling point.	Not available.
Boiling range.	Not available.
Flash point.	> 60 °C.
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Lower inflammability limit.	Not available.
Upper inflammability limit.	Not available.
Lower explosive limit.	Not available.
Upper explosive limit.	Not available.
Vapour pressure.	Not available.
Vapour density	Not available.
Relative density.	1,005
Solubility	partially soluble in water
Partition coefficient: n-octanol/water	Not available.
Auto-ignition temperature.	Not available.
Decomposition temperature.	Not available.
Viscosity	Not available.
Explosive properties	Not available.
Oxidising properties	Not available.

9.2. Other information.

Molecular weight.	20,864
Total solids (250°C / 482°F)	1,52 %
VOC (Directive 2010/75/EC) :	0
VOC (volatile carbon) :	0

SECTION 10. Stability and reactivity.**10.1. Reactivity.**

There are no particular risks of reaction with other substances in normal conditions of use.

SECTION 10. Stability and reactivity. ... / >>

10.2. Chemical stability.

The product is stable in normal conditions of use and storage.

QUINHYDRONE

Heat-sensitive, Sensitivity to light, Sensitive to air.

SODIUM HYDROXIDE

Hygroscopic.

10.3. Possibility of hazardous reactions.

No hazardous reactions are foreseeable in normal conditions of use and storage.

QUINHYDRONE

Violent reactions possible with: Strong oxidizing agents.

POTASSIUM HYDROGEN PHTHALATE

Violent reactions possible with: Strong oxidizing agents, Nitric acid.

SODIUM HYDROXIDE

Risk of explosion/exothermic reaction with: Acetone, Nitriles, phosphides, halogens, halogen-halogen compounds, chlorinated solvents, Ethylene oxide, Hydrazine hydrate, hydroxylamine, anhydrides, Peroxides, Acrolein, Acid chlorides, Acids, sulphuric acid, silver salt, hydrogen peroxide, organic nitro compounds, Water, Metals, Light metals. Possible formation of: Hydrogen. Violent reactions possible with: ammonium compounds, organic combustible substances, phenols. Generates dangerous gases or fumes in contact with: persulfates, Sodium borohydride, Oxides of phosphorus.

10.4. Conditions to avoid.

None in particular. However the usual precautions used for chemical products should be respected.

SODIUM HYDROXIDE

Exposure to the air, moisture and sources of heat.

10.5. Incompatible materials.

SODIUM HYDROXIDE

Strong acids, ammonia, zinc, lead, aluminium, water and flammable liquids.

10.6. Hazardous decomposition products.

Information not available.

SECTION 11. Toxicological information.

11.1. Information on toxicological effects.

ACUTE TOXICITY.

LC50 (Inhalation - vapours) of the mixture:	Not classified (no significant component).
LC50 (Inhalation - mists / powders) of the mixture:	Not classified (no significant component).
LD50 (Oral) of the mixture:	45417,844 mg/kg
LD50 (Dermal) of the mixture:	Not classified (no significant component).

SKIN CORROSION / IRRITATION.

Does not meet the classification criteria for this hazard class.

SERIOUS EYE DAMAGE / IRRITATION.

Does not meet the classification criteria for this hazard class.

RESPIRATORY OR SKIN SENSITISATION.

Does not meet the classification criteria for this hazard class.

GERM CELL MUTAGENICITY.

Does not meet the classification criteria for this hazard class.

CARCINOGENICITY.

SECTION 11. Toxicological information. ... / >>

Does not meet the classification criteria for this hazard class.

REPRODUCTIVE TOXICITY.

Does not meet the classification criteria for this hazard class.

STOT - SINGLE EXPOSURE.

Does not meet the classification criteria for this hazard class.

STOT - REPEATED EXPOSURE.

Does not meet the classification criteria for this hazard class.

ASPIRATION HAZARD.

Does not meet the classification criteria for this hazard class.

SECTION 12. Ecological information.

Use this product according to good working practices. Avoid littering. Inform the competent authorities, should the product reach waterways or contaminate soil or vegetation.

12.1. Toxicity.

Information not available.

12.2. Persistence and degradability.

Information not available.

12.3. Bioaccumulative potential.

Information not available.

12.4. Mobility in soil.

Information not available.

12.5. Results of PBT and vPvB assessment.

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

12.6. Other adverse effects.

Information not available.

SECTION 13. Disposal considerations.

13.1. Waste treatment methods.

Reuse, when possible. Neat product residues should be considered special non-hazardous waste.

Disposal must be performed through an authorised waste management firm, in compliance with national and local regulations.

CONTAMINATED PACKAGING

Contaminated packaging must be recovered or disposed of in compliance with national waste management regulations.

SECTION 14. Transport information.

The product is not dangerous under current provisions of the Code of International Carriage of Dangerous Goods by Road (ADR) and by Rail (RID), of the International Maritime Dangerous Goods Code (IMDG), and of the International Air Transport Association (IATA) regulations.

14.1. UN number.

Not applicable.

14.2. UN proper shipping name.

Not applicable.

SECTION 14. Transport information. ... / >>**14.3. Transport hazard class(es).**

Not applicable.

14.4. Packing group.

Not applicable.

14.5. Environmental hazards.

Not applicable.

14.6. Special precautions for user.

Not applicable.

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code.

Information not relevant.

SECTION 15. Regulatory information.**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture.**Seveso Category - Directive 2012/18/EC: None.Restrictions relating to the product or contained substances pursuant to Annex XVII to EC Regulation 1907/2006.
None.Substances in Candidate List (Art. 59 REACH).

On the basis of available data, the product does not contain any SVHC in percentage greater than 0,1%.

Substances subject to authorisation (Annex XIV REACH).

None.

Substances subject to exportation reporting pursuant to (EC) Reg. 649/2012:

None.

Substances subject to the Rotterdam Convention:

None.

Substances subject to the Stockholm Convention:

None.

Healthcare controls.

Information not available.

WGK 1: Low hazard to waters

15.2. Chemical safety assessment.

No chemical safety assessment has been processed for the mixture and the substances it contains.

SECTION 16. Other information.**LEGEND:**

- ADR: European Agreement concerning the carriage of Dangerous goods by Road
- CAS NUMBER: Chemical Abstract Service Number
- CE50: Effective concentration (required to induce a 50% effect)
- CE NUMBER: Identifier in ESIS (European archive of existing substances)
- CLP: EC Regulation 1272/2008
- DNEL: Derived No Effect Level
- EmS: Emergency Schedule
- GHS: Globally Harmonized System of classification and labeling of chemicals

SECTION 16. Other information. ... / >>

- IATA DGR: International Air Transport Association Dangerous Goods Regulation
- IC50: Immobilization Concentration 50%
- IMDG: International Maritime Code for dangerous goods
- IMO: International Maritime Organization
- INDEX NUMBER: Identifier in Annex VI of CLP
- LC50: Lethal Concentration 50%
- LD50: Lethal dose 50%
- OEL: Occupational Exposure Level
- PBT: Persistent bioaccumulative and toxic as REACH Regulation
- PEC: Predicted environmental Concentration
- PEL: Predicted exposure level
- PNEC: Predicted no effect concentration
- REACH: EC Regulation 1907/2006
- RID: Regulation concerning the international transport of dangerous goods by train
- TLV: Threshold Limit Value
- TLV CEILING: Concentration that should not be exceeded during any time of occupational exposure.
- TWA STEL: Short-term exposure limit
- TWA: Time-weighted average exposure limit
- VOC: Volatile organic Compounds
- vPvB: Very Persistent and very Bioaccumulative as for REACH Regulation
- WGK: Water hazard classes (German).

GENERAL BIBLIOGRAPHY

1. Regulation (EU) 1907/2006 (REACH) of the European Parliament
2. Regulation (EC) 1272/2008 (CLP) of the European Parliament
3. Regulation (EU) 790/2009 (I Atp. CLP) of the European Parliament
4. Regulation (EU) 2015/830 of the European Parliament
5. Regulation (EU) 286/2011 (II Atp. CLP) of the European Parliament
6. Regulation (EU) 618/2012 (III Atp. CLP) of the European Parliament
7. Regulation (EU) 487/2013 (IV Atp. CLP) of the European Parliament
8. Regulation (EU) 944/2013 (V Atp. CLP) of the European Parliament
9. Regulation (EU) 605/2014 (VI Atp. CLP) of the European Parliament
10. Regulation (EU) 2015/1221 (VII Atp. CLP) of the European Parliament

- The Merck Index. - 10th Edition
- Handling Chemical Safety
- INRS - Fiche Toxicologique (toxicological sheet)
- Patty - Industrial Hygiene and Toxicology
- N.I. Sax - Dangerous properties of Industrial Materials-7, 1989 Edition
- ECHA website

Note for users:

The information contained in the present sheet are based on our own knowledge on the date of the last version. Users must verify the suitability and thoroughness of provided information according to each specific use of the product.

This document must not be regarded as a guarantee on any specific product property.

The use of this product is not subject to our direct control; therefore, users must, under their own responsibility, comply with the current health and safety laws and regulations. The producer is relieved from any liability arising from improper uses.

Provide appointed staff with adequate training on how to use chemical products.

Changes to previous review:

The following sections were modified:

01 / 02 / 04 / 06 / 09 / 10 / 11 / 12 / 14 / 15.