

Datasheet

RS 2 Core Screened Microphone Cable, 60 V, 3.7mm od

RS Stock No. 748-1942



Product Description

Application:

For Microphone Cable

Multi-construction

2 Core

Construction

2 Core	Tinned Copper
Construction	T0.2±0.008×7
Stranded Dia.(mm)	0.60
Insulation 1	PE
Thickness	0.25
Insulation Dia.(mm)	1.1±0.08×2C Twist
Insulation Color	Natrual, Blue
Filler	Cotton rope
Drain Wire	Tinned Copper
Construction(mm)	T0.2±0.008×7
Insulation 2	Semi-Conductive PE
Thickness	0.25
Insulation Dia.(mm)	2.7±0.15
Insulation Color	Black
Jacket	PVC
Thickness(mm)	0.40
Dia.(±0.15mm)	3.70
Jacket Color	Black


Marking(white ink; once/meter)

2 Core Microphone Cable PVC [Weekyear] [Metermark]

PACKAGING

100M/Reel

Design



Electrical Characteristics

Max.Conductor DC Resistance at 20 °C (Ω /Km)	<92
Rated Temperature(°C)	-20~70
Rated Voltage (V)	60
Min.Insulation DC Resistance at 20 °C ($M\Omega$ *Km)	>200
Nomial Capacitance(pF/M)	
Core to Core	90
Core to Screen	150