

PCB terminal block - SPT 2,5/ 7-H-5,0-EX - 1732438

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

PCB terminal block, Nominal current (Ex): 23 A, Nominal voltage (Ex): 176 V, Pitch: 5 mm, Number of positions: 7, Connection method: Spring-cage connection, Mounting: Soldering, Color: green




Why buy this product

- ✓ Two solder pins for a high level of stability on the PCB
- ✓ Voltage can be increased by using pitch spacers
- ✓ Front Push-in spring-cage connection
- ✓ Push-in direct plug-in technology for solid and stranded conductors with ferrules



Key commercial data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 282970
Weight per Piece (excluding packing)	6.98 g
Custom tariff number	85369010
Country of origin	Poland
Note	Made to Order (non-returnable)

Technical data

Dimensions

Pitch	5 mm
Dimension a	30 mm
Pin dimensions	0,8 x 0,8
Pin spacing	5 mm
Hole diameter	1.1 mm

General

Range of articles	SPT 2,5/...-H-EX
Insulating material group	I
Nominal cross section	2.5 mm ²

PCB terminal block - SPT 2,5/ 7-H-5,0-EX - 1732438

Technical data

General

Insulating material	PA
Solder pin surface	Sn
Inflammability class according to UL 94	V0
Number of positions	7

Classifications

eCl@ss

eCl@ss 4.0	27141111
eCl@ss 4.1	27141109
eCl@ss 5.0	27141190
eCl@ss 5.1	27141190
eCl@ss 6.0	27261101
eCl@ss 7.0	27440401
eCl@ss 8.0	27440401

ETIM


ETIM 3.0	EC001121
ETIM 4.0	EC002643
ETIM 5.0	EC002643

UNSPSC

UNSPSC 6.01	30211801
UNSPSC 7.0901	39121432
UNSPSC 11	39121432
UNSPSC 12.01	39121432
UNSPSC 13.2	39121432

Drawings

Drilling diagram



Dimensioned drawing

