

## N-Channel UltraFET Power MOSFET 55 V, 20 A, 26 mΩ

These N-Channel power MOSFETs are manufactured using the innovative UltraFET process. This advanced process technology achieves the lowest possible on-resistance per silicon area, resulting in outstanding performance. This device is capable of withstanding high energy in the avalanche mode and the diode exhibits very low reverse recovery time and stored charge. It was designed for use in applications where power efficiency is important, such as switching regulators, switching converters, motor drivers, relay drivers, low-voltage bus switches, and power management in portable and battery-operated products.

Formerly developmental type TA75329.


### Ordering Information

| PART NUMBER  | PACKAGE  | BRAND  |
|--------------|----------|--------|
| HUF75329D3ST | TO-252AA | 75329D |

### Features


- 20A, 55V
- Simulation Models
  - Temperature Compensated PSPICE® and SABER™ Models
  - SPICE and SABER Thermal Impedance Models Available on the WEB at: [www.fairchildsemi.com](http://www.fairchildsemi.com)
- Peak Current vs Pulse Width Curve
- UIS Rating Curve
- Related Literature
  - TB334, "Guidelines for Soldering Surface Mount Components to PC Boards"

### Symbol



### Packaging

JEDEC TO-252AA



Product reliability information can be found at <http://www.fairchildsemi.com/products/discrete/reliability/index.html>

For severe environments, see our Automotive HUFA series.

All Fairchild semiconductor products are manufactured, assembled and tested under ISO9000 and QS9000 quality systems certification.

# HUF75329D3S

## Absolute Maximum Ratings $T_C = 25^{\circ}\text{C}$ , Unless Otherwise Specified

|                                                                          |                | UNITS                            |
|--------------------------------------------------------------------------|----------------|----------------------------------|
| Drain to Source Voltage (Note 1) . . . . .                               | $V_{DS}$       | 55 V                             |
| Drain to Gate Voltage ( $R_{GS} = 20\text{k}\Omega$ ) (Note 1) . . . . . | $V_{DGR}$      | 55 V                             |
| Gate to Source Voltage . . . . .                                         | $V_{GS}$       | $\pm 20$ V                       |
| Drain Current                                                            |                |                                  |
| Continuous (Figure 2) . . . . .                                          | $I_D$          | 20 A                             |
| Pulsed Drain Current . . . . .                                           | $I_{DM}$       | Figure 4                         |
| Pulsed Avalanche Rating . . . . .                                        | $E_{AS}$       | Figure 6                         |
| Power Dissipation . . . . .                                              | $P_D$          | 128 W                            |
| Derate Above $25^{\circ}\text{C}$ . . . . .                              |                | 0.86 $\text{W}/^{\circ}\text{C}$ |
| Operating and Storage Temperature . . . . .                              | $T_J, T_{STG}$ | $-55$ to $175^{\circ}\text{C}$   |
| Maximum Temperature for Soldering                                        |                |                                  |
| Leads at 0.063in (1.6mm) from Case for 10s. . . . .                      | $T_L$          | 300 $^{\circ}\text{C}$           |
| Package Body for 10s, See Techbrief 334 . . . . .                        | $T_{pkg}$      | 260 $^{\circ}\text{C}$           |

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

### NOTE:

1.  $T_J = 25^{\circ}\text{C}$  to  $150^{\circ}\text{C}$ .

## Electrical Specifications $T_C = 25^{\circ}\text{C}$ , Unless Otherwise Specified

| PARAMETER                                        | SYMBOL              | TEST CONDITIONS                                                                                                         | MIN                                                                                                                    | TYP   | MAX   | UNITS            |    |
|--------------------------------------------------|---------------------|-------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------|-------|-------|------------------|----|
| OFF STATE SPECIFICATIONS                         |                     |                                                                                                                         |                                                                                                                        |       |       |                  |    |
| Drain to Source Breakdown Voltage                | BV <sub>DSS</sub>   | I <sub>D</sub> = 250μA, V <sub>GS</sub> = 0V (Figure 11)                                                                | 55                                                                                                                     | -     | -     | V                |    |
| Zero Gate Voltage Drain Current                  | I <sub>DSS</sub>    | V <sub>DS</sub> = 50V, V <sub>GS</sub> = 0V                                                                             | -                                                                                                                      | -     | 1     | μA               |    |
|                                                  |                     | V <sub>DS</sub> = 45V, V <sub>GS</sub> = 0V, T <sub>C</sub> = 150 <sup>0</sup> C                                        | -                                                                                                                      | -     | 250   | μA               |    |
| Gate to Source Leakage Current                   | I <sub>GSS</sub>    | V <sub>GS</sub> = ±20V                                                                                                  | -                                                                                                                      | -     | ±100  | nA               |    |
| ON STATE SPECIFICATIONS                          |                     |                                                                                                                         |                                                                                                                        |       |       |                  |    |
| Gate to Source Threshold Voltage                 | V <sub>GS(TH)</sub> | V <sub>GS</sub> = V <sub>DS</sub> , I <sub>D</sub> = 250μA (Figure 10)                                                  | 2                                                                                                                      | -     | 4     | V                |    |
| Drain to Source On Resistance                    | r <sub>DS(ON)</sub> | I <sub>D</sub> = 20A, V <sub>GS</sub> = 10V (Figure 9)                                                                  | -                                                                                                                      | 0.022 | 0.026 | Ω                |    |
| THERMAL SPECIFICATIONS                           |                     |                                                                                                                         |                                                                                                                        |       |       |                  |    |
| Thermal Resistance Junction to Case              | R <sub>θJC</sub>    | (Figure 3)                                                                                                              | -                                                                                                                      | -     | 1.17  | <sup>0</sup> C/W |    |
| Thermal Resistance Junction to Ambient           | R <sub>θJA</sub>    | TO-252                                                                                                                  | -                                                                                                                      | -     | 100   | <sup>0</sup> C/W |    |
| SWITCHING SPECIFICATIONS (V <sub>GS</sub> = 10V) |                     |                                                                                                                         |                                                                                                                        |       |       |                  |    |
| Turn-On Time                                     | t <sub>ON</sub>     | V <sub>DD</sub> = 30V, I <sub>D</sub> ≅ 20A,<br>R <sub>L</sub> = 1.5Ω, V <sub>GS</sub> = 10V,<br>R <sub>GS</sub> = 9.1Ω | -                                                                                                                      | -     | 60    | ns               |    |
| Turn-On Delay Time                               | t <sub>d(ON)</sub>  |                                                                                                                         | -                                                                                                                      | 7     | -     | ns               |    |
| Rise Time                                        | t <sub>r</sub>      |                                                                                                                         | -                                                                                                                      | 30    | -     | ns               |    |
| Turn-Off Delay Time                              | t <sub>d(OFF)</sub> |                                                                                                                         | -                                                                                                                      | 10    | -     | ns               |    |
| Fall Time                                        | t <sub>f</sub>      |                                                                                                                         | -                                                                                                                      | 33    | -     | ns               |    |
| Turn-Off Time                                    | t <sub>OFF</sub>    |                                                                                                                         | -                                                                                                                      | -     | 65    | ns               |    |
| GATE CHARGE SPECIFICATIONS                       |                     |                                                                                                                         |                                                                                                                        |       |       |                  |    |
| Total Gate Charge                                | Q <sub>g(TOT)</sub> | V <sub>GS</sub> = 0V to 20V                                                                                             | V <sub>DD</sub> = 30V,<br>I <sub>D</sub> ≅ 20A,<br>R <sub>L</sub> = 1.5Ω<br>I <sub>g(REF)</sub> = 1.0mA<br>(Figure 13) | -     | 50    | 65               | nC |
| Gate Charge at 10V                               | Q <sub>g(10)</sub>  | V <sub>GS</sub> = 0V to 10V                                                                                             |                                                                                                                        | -     | 32    | 40               | nC |
| Threshold Gate Charge                            | Q <sub>g(TH)</sub>  | V <sub>GS</sub> = 0V to 2V                                                                                              |                                                                                                                        | -     | 2.0   | 2.5              | nC |
| Gate to Source Gate Charge                       | Q <sub>gs</sub>     |                                                                                                                         |                                                                                                                        | -     | 5     | -                | nC |
| Reverse Transfer Capacitance                     | Q <sub>gd</sub>     |                                                                                                                         |                                                                                                                        | -     | 13    | -                | nC |

# HUF75329D3S

## Electrical Specifications $T_C = 25^\circ\text{C}$ , Unless Otherwise Specified

| PARAMETER                         | SYMBOL    | TEST CONDITIONS                                                                    | MIN | TYP  | MAX | UNITS |
|-----------------------------------|-----------|------------------------------------------------------------------------------------|-----|------|-----|-------|
| <b>CAPACITANCE SPECIFICATIONS</b> |           |                                                                                    |     |      |     |       |
| Input Capacitance                 | $C_{ISS}$ | $V_{DS} = 25\text{V}$ , $V_{GS} = 0\text{V}$ ,<br>$f = 1\text{MHz}$<br>(Figure 12) | -   | 1060 | -   | pF    |
| Output Capacitance                | $C_{OSS}$ |                                                                                    | -   | 405  | -   | pF    |
| Reverse Transfer Capacitance      | $C_{RSS}$ |                                                                                    | -   | 95   | -   | pF    |

## Source to Drain Diode Specifications

| PARAMETER                     | SYMBOL   | TEST CONDITIONS                                                | MIN | TYP | MAX  | UNITS |
|-------------------------------|----------|----------------------------------------------------------------|-----|-----|------|-------|
| Source to Drain Diode Voltage | $V_{SD}$ | $I_{SD} = 20\text{A}$                                          | -   | -   | 1.25 | V     |
| Reverse Recovery Time         | $t_{rr}$ | $I_{SD} = 20\text{A}$ , $dI_{SD}/dt = 100\text{A}/\mu\text{s}$ | -   | -   | 68   | ns    |
| Reverse Recovered Charge      | $Q_{RR}$ | $I_{SD} = 20\text{A}$ , $dI_{SD}/dt = 100\text{A}/\mu\text{s}$ | -   | -   | 120  | nC    |

## Typical Performance Curves




FIGURE 1. NORMALIZED POWER DISSIPATION vs CASE TEMPERATURE




FIGURE 2. MAXIMUM CONTINUOUS DRAIN CURRENT vs CASE TEMPERATURE




FIGURE 3. NORMALIZED MAXIMUM TRANSIENT THERMAL IMPEDANCE

## Typical Performance Curves (Continued)




FIGURE 4. PEAK CURRENT CAPABILITY





FIGURE 5. FORWARD BIAS SAFE OPERATING AREA



NOTE: Refer to Fairchild Application Notes AN9321 and AN9322.

FIGURE 6. UNCLAMPED INDUCTIVE SWITCHING CAPABILITY




FIGURE 7. SATURATION CHARACTERISTICS




FIGURE 8. TRANSFER CHARACTERISTICS

# Typical Performance Curves (Continued)




FIGURE 9. NORMALIZED DRAIN TO SOURCE ON RESISTANCE vs JUNCTION TEMPERATURE




FIGURE 10. NORMALIZED GATE THRESHOLD VOLTAGE vs JUNCTION TEMPERATURE




FIGURE 11. NORMALIZED DRAIN TO SOURCE BREAKDOWN VOLTAGE vs JUNCTION TEMPERATURE





FIGURE 12. CAPACITANCE vs DRAIN TO SOURCE VOLTAGE



NOTE: Refer to Fairchild Application Notes AN7254 and AN7260.

FIGURE 13. GATE CHARGE WAVEFORMS FOR CONSTANT GATE CURRENT

## Test Circuits and Waveforms




FIGURE 14. UNCLAMPED ENERGY TEST CIRCUIT




FIGURE 15. UNCLAMPED ENERGY WAVEFORMS




FIGURE 16. GATE CHARGE TEST CIRCUIT




FIGURE 17. GATE CHARGE WAVEFORM




FIGURE 18. SWITCHING TIME TEST CIRCUIT




FIGURE 19. RESISTIVE SWITCHING WAVEFORMS

**PSPICE Electrical Model**

.SUBCKT HUF75329D 2 1 3 ; rev 6/19/97

CA 12 8 1.72e-9  
 CB 15 14 1.52e-9  
 CIN 6 8 9.61e-10

DBODY 7 5 DBODYMOD  
 DBREAK 5 11 DBREAKMOD  
 DPLCAP 10 5 DPLCAPMOD

EBREAK 11 7 17 18 58.13  
 EDS 14 8 5 8 1  
 EGS 13 8 6 8 1  
 ESG 6 10 6 8 1  
 EVTHRES 6 21 19 8 1  
 EVTEMP 20 6 18 22 1

IT 8 17 1

LDRAIN 2 5 1e-9  
 LGATE 1 9 2.86e-9  
 LSOURCE 3 7 2.69e-9

MMED 16 6 8 8 MMEDMOD  
 MSTRO 16 6 8 8 MSTROMOD  
 MWEAK 16 21 8 8 MWEAKMOD

RBREAK 17 18 RBREAKMOD 1  
 RDRAIN 50 16 RDRAINMOD 1e-3  
 RGATE 9 20 1.52  
 RLDRAIN 2 5 10  
 RLGate 1 9 26.9  
 RLSOURCE 3 7 28.6  
 RSLC1 5 51 RSLCMOD 1e-6  
 RSLC2 5 50 1e3  
 RSOURCE 8 7 RSOURCEMOD 13.85e-3  
 RVTHRES 22 8 RVTHRESMOD 1  
 RVTEMP 18 19 RVTEMPMOD 1

S1A 6 12 13 8 S1AMOD  
 S1B 13 12 13 8 S1BMOD  
 S2A 6 15 14 13 S2AMOD  
 S2B 13 15 14 13 S2BMOD

VBAT 22 19 DC 1


ESLC 51 50 VALUE={{(V(5,51)/ABS(V(5,51)))}}\*(PWR(V(5,51)/(1e-6\*135),3.5))}

.MODEL DBODYMOD D (IS = 7.50e-13 RS = 5.05e-3 TRS1 = 2.21e-3 TRS2 = 1.02e-6 CJO = 1.51e-9 TT = 4.05e-8 M = 0.5)  
 .MODEL DBREAKMOD D (RS = 2.14e-1 TRS1 = 9.62e-4 TRS2 = 1.23e-6)  
 .MODEL DPLCAPMOD D (CJO = 13.5e-1 OIS = 1e-3 ON = 10 M = 0.85)  
 .MODEL MMEDMOD NMOS (VTO = 3.25 KP = 2.50 IS = 1e-30 N = 10 TOX = 1 L = 1u W = 1u RG = 1.52)  
 .MODEL MSTROMOD NMOS (VTO = 3.80 KP = 70.0 IS = 1e-30 N = 10 TOX = 1 L = 1u W = 1u)  
 .MODEL MWEAKMOD NMOS (VTO = 2.91 KP = 0.06 IS = 1e-30 N = 10 TOX = 1 L = 1u W = 1u RG = 15.2 RS = 0.1)  
 .MODEL RBREAKMOD RES (TC1 = 1.05e-3 TC2 = 1.94e-7)  
 .MODEL RDRAINMOD RES (TC1 = 8.04e-2 TC2 = 1.37e-4)  
 .MODEL RSLCMOD RES (TC1 = 4.83e-3 TC2 = 1.16e-6)  
 .MODEL RSOURCEMOD RES (TC1 = 0 TC2 = 0)  
 .MODEL RVTHRESMOD RES (TC = -3.43e-3 TC2 = -1.63e-5)  
 .MODEL RVTEMPMOD RES (TC1 = -1.35e-3 TC2 = 1.16e-6)

.MODEL S1AMOD VSWITCH (RON = 1e-5 ROFF = 0.1 VON = -7.90 VOFF = -4.90)  
 .MODEL S1BMOD VSWITCH (RON = 1e-5 ROFF = 0.1 VON = -4.90 VOFF = -7.90)  
 .MODEL S2AMOD VSWITCH (RON = 1e-5 ROFF = 0.1 VON = -0.50 VOFF = 2.50)  
 .MODEL S2BMOD VSWITCH (RON = 1e-5 ROFF = 0.1 VON = 2.50 VOFF = -0.50)

.ENDS

NOTE: For further discussion of the PSPICE model, consult **A New PSPICE Sub-Circuit for the Power MOSFET Featuring Global Temperature Options**; IEEE Power Electronics Specialist Conference Records, 1991, written by William J. Hepp and C. Frank Wheatley.







**SPICE Thermal Model**

REV 23 February 1999

HUF75329D

CTHERM1 th 6 2.80e-3  
 CTHERM2 6 5 1.00e-2  
 CTHERM3 5 4 6.80e-3  
 CTHERM4 4 3 7.00e-3  
 CTHERM5 3 2 1.60e-2  
 CTHERM6 2 tl 15.55

RTHERM1 th 6 7.94e-3  
 RTHERM2 6 5 1.98e-2  
 RTHERM3 5 4 5.57e-2  
 RTHERM4 4 3 3.13e-1  
 RTHERM5 3 2 4.71e-1  
 RTHERM6 2 tl 6.26e-2


**SABER Thermal Model**

SABER thermal model HUF75329D

```
template thermal_model th tl
thermal_c th, tl
```

```
{
  ctherm.ctherm1 th 6 = 2.80e-3
  ctherm.ctherm2 6 5 = 1.00e-2
  ctherm.ctherm3 5 4 = 6.80e-3
  ctherm.ctherm4 4 3 = 7.00e-3
  ctherm.ctherm5 3 2 = 1.60e-2
  ctherm.ctherm6 2 tl = 15.55
```

```
  rtherm.rtherm1 th 6 = 7.94e-3
  rtherm.rtherm2 6 5 = 1.98e-2
  rtherm.rtherm3 5 4 = 5.57e-2
  rtherm.rtherm4 4 3 = 3.13e-1
  rtherm.rtherm5 3 2 = 4.71e-1
  rtherm.rtherm6 2 tl = 6.26e-2
}
```





## TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

|                                                                                   |                                                 |                                       |                  |
|-----------------------------------------------------------------------------------|-------------------------------------------------|---------------------------------------|------------------|
| AccuPower™                                                                        | F-PFS™                                          | PowerTrench®                          | Sync-Lock™       |
| AX-CAP®*                                                                          | FRFET®                                          | PowerXS™                              | SYSTEM GENERAL®* |
| BitSiC™                                                                           | Global Power ResourceSM                         | Programmable Active Droop™            | TinyBoost®       |
| Build it Now™                                                                     | GreenBridge™                                    | QFET®                                 | TinyBuck®        |
| CorePLUS™                                                                         | Green FPS™                                      | QS™                                   | TinyCalc™        |
| CorePOWER™                                                                        | Green FPS™ e-Series™                            | Quiet Series™                         | TinyLogic®       |
| CROSSVOLT™                                                                        | Gmax™                                           | RapidConfigure™                       | TINYOPTO™        |
| CTL™                                                                              | GTO™                                            | Saving our world, 1mW/W/kW at a time™ | TinyPower™       |
| Current Transfer Logic™                                                           | IntelliMAX™                                     | SignalWise™                           | TinyPWM™         |
| DEUXPEED®                                                                         | ISOPLANAR™                                      | SmartMax™                             | TinyWire™        |
| Dual Cool™                                                                        | Marking Small Speakers Sound Louder and Better™ | SMART START™                          | TranSiC™         |
| EcoSPARK®                                                                         | MegaBuck™                                       | Solutions for Your Success™           | TriFault Detect™ |
| EfficientMax™                                                                     | MICROCOUPLER™                                   | SPM®                                  | TRUECURRENT®*    |
| ESBC™                                                                             | MicroFET™                                       | STEALTH™                              | µSerDes™         |
|  | MicroPak™                                       | SuperFET®                             | UHC®             |
| Fairchild®                                                                        | MicroPak2™                                      | SuperSOT™-3                           | Ultra FRFET™     |
| Fairchild Semiconductor®                                                          | MillerDrive™                                    | SuperSOT™-6                           | UniFET™          |
| FACT Quiet Series™                                                                | MotionMax™                                      | SuperSOT™-8                           | VCX™             |
| FACT®                                                                             | mWSaver®                                        | SupreMOS®                             | VisualMax™       |
| FAST®                                                                             | OptoHiT™                                        | SyncFET™                              | VoltagePlus™     |
| FastvCore™                                                                        | OPTOLOGIC®                                      |                                       | XS™              |
| FETBench™                                                                         | OPTOPLANAR®                                     |                                       |                  |
| FPS™                                                                              |                                                 |                                       |                  |

\*Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

## DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used here in:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

## ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, [www.Fairchildsemi.com](http://www.Fairchildsemi.com), under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufactures of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed application, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address and warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

## PRODUCT STATUS DEFINITIONS

### Definition of Terms

| Datasheet Identification | Product Status        | Definition                                                                                                                                                                                          |
|--------------------------|-----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Advance Information      | Formative / In Design | Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.                                                                       |
| Preliminary              | First Production      | Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design. |
| No Identification Needed | Full Production       | Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.                                               |
| Obsolete                 | Not In Production     | Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.                                                    |

Rev. 166