


Cam followers



Dimensions				Basic load ratings		Fatigue load limit	Maximum radial loads		Limiting speed	Mass	Designation
D	d	B	C	dynamic C	static C ₀	P _u	dynamic F _r	static F _{0r}	r/min	kg	-
mm				kN		kN	kN				
62	24	80	29	24,6	44	5,5	58,5	85	2400	0,77	KR 62 PPA



Appertaining grease nipple(s)

NIP A3x9.5

Appertaining hexagonal nut

Size, mm

M 24x1.5

Rec. tightening torque, Nm

220

Internal hexagon in stud

Key width, mm

14