

1 ATTENUATION ≤ 0.3 dB, MEASURED AT 850 nm OR 1300 nm
 ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B

2 RETURN LOSS ≥ 20 dB, IN MATED CONDITION
 AGAINST REFERENCE CONNECTOR AT 850 nm OR 1300 nm

3 TEST RESULT SHEET IS SUPPLIED WITH EACH INDIVIDUAL PACKED ASSEMBLY


4 CABLE INFORMATION:

- CORE DIAMETER: 62.5/125 μ m
- OUTER JACKET DIAMETER: 1.8x3.6 mm
- OUTER JACKET COLOUR: GREY
- OUTER JACKET MATERIAL: LSZH

5 BLANK LABEL

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-2061309-Y	XY.0

2	BLANK LABEL	3
2	LC DUPLEX CONNECTOR, MULTI MODE, BEIGE	2
L	FOCAB 1.8MZ 62.5/125, GREY, LSZH	1
Qty	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 16OCT2009 CHK A. HENGELMOLEN 16OCT2009 APVD A. HENGELMOLEN 16OCT2009		 Tyco Electronics Corporation 's-Hertogenbosch, Nederland	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		FIBER OPTIC LEAD 1.8MZ LC/DPX - LC/DPX MULTI MODE 62.5/125	
MATERIAL		FINISH		SIZE CAGE CODE DRAWING NO	
-		-		A2 00779 C-2061309	
WEIGHT		-		RESTRICTED TO	
-		-		-	
CUSTOMER DRAWING				SCALE NTS SHEET 1 OF 1 REV A	