



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		T3	REVISED PER ECO-11-004820	11MAR11	RK	HMR

D

C

B

A



- 1 STAMP "AMP - SEE TABLE" APPROX AS SHOWN
- 2 WIRE INSULATION DIA: SEE TABLE
- 3 TONGUE MATERIAL THK: .040±.002
- 4 BODY: TIN PLATE .000100 MIN EXT THK PER ASTM B545
- 5 SLEEVE: TIN PLATE .000100 MIN EXT THK PER ASTM B545
- 6 SLEEVE: NICKEL PLATE PER QQ-N-290
- 7 BODY & SLEEVE- CU PER ASTM B152
INSULATION - NYLON PER ASTM D4066
COLOR - YELLOW
- 8 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE.
- 9 MEETS MS25036-113, CLASS 1 & 2
- 10 MEETS MS25036-113, CLASS 2
- 11 MEETS M7928/1-60, CLASS 1 & 2
- 12 MEETS M7928/1-67, CLASS 1 & 2

50	LOOSE PIECE, BOX	12-10	.150-.230	12-10	--	A	4	6	8-320576-2
500	LOOSE PIECE LG BOX	12-10	.150-.230	12-10	--	A		5	2-320576-6
2500	ON TAPE & REEL	10	.119-.200	10	BROWN	B		6	2-320576-5
2500	ON TAPE & REEL	12	.095-.200	12	YELLOW	B		6	2-320576-4
---	LOOSE PIECE	10	.119-.200	10	BROWN	B		6	12 2-320576-3
---	LOOSE PIECE	12	.095-.200	12	YELLOW	B		6	11 2-320576-2
2500	ON TAPE & REEL	12-10	.150-.230	12-10	--	A		5	10 2-320576-1
---	LOOSE PIECE	12-10	.150-.230	12-10	--	A		5	320576
QTY	PACKAGE TYPE	STAMPING	WIRE INSUL DIA	WIRE SIZE	STRIPE COLOR	STYLE	BODY	SLEEVE	PART NO
							FINISH		

OPERATING TEMPERATURE		THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN JR RUTH 23DEC09	TE TE Connectivity			
MAXIMUM RECOMMENDED OPERATING TEMPERATURE		DIMENSIONS: INCHES			CHK T MICHELUTTI 23DEC09				
WIRE SIZE: 12-10 AWG				TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± -		APVD T MICHELUTTI 23DEC09		NAME	
						PRODUCT SPEC		TERMINAL, RING TONGUE, PIDG WIRE SIZE: 12-10 AWG	
						APPLICATION SPEC		SIZE	
MATERIAL		FINISH		WEIGHT		A2	CAGE CODE	DRAWING NO	RESTRICTED TO
-		-		-			00779	C-320576	-
CUSTOMER DRAWING						SCALE		SHEET	REV
						5:1		1 of 1	T3