



### Slim Line® Series Panel Mount

Slim-Line® products are a unique series of premium quality connectors featuring interchangeable inserts which allow any plug or receptacle to be male or female. Offered with metal housings and captive coupling rings to provide secure mechanical connection, Slim Lines are available in 2-5 conductors.

---

#### Materials

- Receptacle Housings: Die-cast zinc, nickel-plated.
- Cord Plug Housings: Copper alloy, nickel-plated.
- Inserts: Glass-reinforced thermoplastic. UL 94 V-0.
- Female Contacts: Copper alloy, silver-plated, solder lug type.
- Pins: Copper alloy, silver-plated, solder cup type.
- Cable Clamp, Strain Relief, and Mounting Hardware: Steel, plated.
- Latch: Steel, plated.

#### Electrical

- Current Rating: 5 Amps carry only.

#### Mounting

- Receptacles: Flange mount type mounts in panels or chassis up to .188 inches (4.78 mm) thick. .125 inch (3.18 mm) diameter holes accept #4 machine screws or .125 inch (3.18 mm) diameter rivets. Rear and front of panel types mount in "D"-shaped hole in panels or chassis up to .219 inches (5.56 mm) thick. Hex nut (SL01), lockwasher (SL02), and flat washer (SL03) are supplied for mounting.

#### Cable Clamp and Strain Relief

- Receptacles: Receptacles are not supplied standard with cable clamp for strain relief. If grounding/shielding feature is desired, separate Cable Clamp, SL04, is installed on receptacle insert.