

74 06 180

High Leverage Diagonal Cutter



- with integrated forged axle for heaviest duty
- suitable for all types of wire including piano wire
- high cutting performance with minimum effort due to optimum co-ordination of the cutting edge angle and transmission ratio
- precision cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, oil-hardened



20 % less effort required

compared to conventional diagonal cutters of the same length.

With integrated forged joint axle.

Article No.	74 06 180
EAN	4003773022985
Pliers	chrome plated
Handles	insulated with multi-component grips, VDE-tested
Style	0
Head	
Insulation standard	IEC 60900 DIN EN 60900
medium hard wire Ø mm	3,8
hard wire Ø mm	2,7
piano wire Ø mm	2,2
Length mm	180
Net weight g	280

technical change and errors excepted

