

Plug - STB 3/4-ST-5,08 - 1752043

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

PCB connector, number of positions: 4, pitch: 5.08 mm, color: green



Key Commercial Data

Packing unit	50 pc
GTIN	 4 017918 028367
GTIN	4017918028367
Weight per Piece (excluding packing)	11.710 g
Custom tariff number	85366990
Country of origin	Poland

Technical data

Dimensions

Length [l]	21 mm
Width [w]	20.32 mm
Height [h]	19 mm
Pitch	5.08 mm
Dimension a	10.16 mm

General

Range of articles	STB
Number of positions	4
Connection method	Screw connection with tension sleeve
Nominal cross section	2.5 mm ²
Stripping length	8 mm
Screw thread	M3

Connection data

Minimum AWG according to UL/CUL	30
Maximum AWG according to UL/CUL	14

Standards and Regulations

Connection in acc. with standard	CSA
----------------------------------	-----

Environmental Product Compliance

Plug - STB 3/4-ST-5,08 - 1752043

Technical data

Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260700
eCl@ss 6.0	27260700
eCl@ss 7.0	27440309
eCl@ss 8.0	27440309
eCl@ss 9.0	27440309

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002498
ETIM 5.0	EC002637
ETIM 6.0	EC002638
ETIM 7.0	EC002638

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

CSA / UL Recognized / EAC

Ex Approvals

Plug - STB 3/4-ST-5,08 - 1752043

Approvals

Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	13631
Nominal voltage UN		300 V	
Nominal current IN		10 A	
mm ² /AWG/kcmil		28-14	

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 60425
Nominal voltage UN		300 V	
Nominal current IN		10 A	
mm ² /AWG/kcmil		30-14	

EAC			B.01742
-----	--	--	---------

Accessories

Accessories

Insulating sleeve

Insulating sleeve - MPS-IH WH - 0201663

Insulating sleeve, color: white



Insulating sleeve - MPS-IH RD - 0201676

Insulating sleeve, color: red



Plug - STB 3/4-ST-5,08 - 1752043

Accessories

Insulating sleeve - MPS-IH GN - 0201702

Insulating sleeve, color: green



Insulating sleeve - MPS-IH BK - 0201731

Insulating sleeve, color: black



Labeled terminal marker

Marker pin Zack strip - BNB-ZB 5,LGS:FORTL.ZAHLEN - 1400201



Marker pin Zack strip, Strip, white, labeled, printed horizontally: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 491 ... 500, mounting type: Plug in, for terminal block width: 5 mm, lettering field size: 4 x 4 mm

Marker pen

Marker pen - B-STIFT - 1051993



Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm

PCB plug

Printed-circuit board connector - CS-STB - 1750142

Coding profile, for plugging into the coding ribs of the plug at a later date, insulating material, color: Red

Terminal marking

Plug - STB 3/4-ST-5,08 - 1752043

Accessories

Marker pin Zack strip - BN-ZB 5/WH:UNBEDRUCKT - 1400078



Marker pin Zack strip, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, mounting type: Plug in, for terminal block width: 5 mm, lettering field size: 4 x 4 mm

Test plug terminal block

Test plugs - MPS-MT - 0201744



Test plugs, with solder connection up to 1 mm² conductor cross section, color: gray

Reducing plug - RPS - 0201647



Reducing plug, color: gray