


Ordering number FA10887_TINA-RS

| | | | |
|-----------------|----------|-------------|------------|
| Family | Tina | FWHM | 10 degrees |
| Type | Assembly | Efficiency | 93 % |
| LED | XP-E | cd/lm | 18.300 |
| Color | White | Gerber File | Available |
| Diameter | 16.1 mm | | |
| Height | 9.7 mm | | |
| Style | Round | | |
| Optic Material | PMMA | | |
| Holder Material | PC | | |
| Fastening | Tape | | |
| Status | Ready | | |


Ordering number FA10644_TINA-D

| | | | |
|-----------------|----------|-------------|------------|
| Family | Tina | FWHM | 14 degrees |
| Type | Assembly | Efficiency | 93 % |
| LED | XP-E | cd/lm | 9.580 |
| Color | White | Gerber File | Available |
| Diameter | 16.1 mm | | |
| Height | 9.7 mm | | |
| Style | Round | | |
| Optic Material | PMMA | | |
| Holder Material | PC | | |
| Fastening | Tape | | |
| Status | Ready | | |


Ordering number FA10645_TINA-M

| | | | |
|-----------------|----------|-------------|------------|
| Family | Tina | FWHM | 30 degrees |
| Type | Assembly | Efficiency | 91 % |
| LED | XP-E | cd/lm | 2.440 |
| Color | White | Gerber File | Available |
| Diameter | 16.1 mm | | |
| Height | 9.7 mm | | |
| Style | Round | | |
| Optic Material | PMMA | | |
| Holder Material | PC | | |
| Fastening | Tape | | |
| Status | Ready | | |


Ordering number FA11200_TINA-O

| | | | |
|-----------------|----------|-------------|---------------|
| Family | Tina | FWHM | 33+15 degrees |
| Type | Assembly | Efficiency | 93 % |
| LED | XP-E | cd/lm | 3.750 |
| Color | White | Gerber File | Available |
| Diameter | 16.1 mm | | |
| Height | 9.7 mm | | |
| Style | Round | | |
| Optic Material | PMMA | | |
| Holder Material | PC | | |
| Fastening | Tape | | |
| Status | Ready | | |

**Ordering number FA11019_TINA-WW**

| | | | |
|-----------------|----------|-------------|------------|
| Family | Tina | FWHM | 58 degrees |
| Type | Assembly | Efficiency | 93 % |
| LED | XP-E | cd/lm | 0.800 |
| Color | White | Gerber File | Available |
| Diameter | 16.1 mm | | |
| Height | 9.7 mm | | |
| Style | Round | | |
| Optic Material | PMMA | | |
| Holder Material | PC | | |
| Fastening | Tape | | |
| Status | Ready | | |

NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.



PRODUCT DATASHEET

Tina series

last update 13/11/2012

GENERAL INFORMATION

- Product series especially designed & optimized for XP-E series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.

Please find more information about used material from below:

http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20UL94_Yellow%20Card.pdf

<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20PLEXIGLAS-Datasheet.pdf>

- Optic holder molded by high quality PC material (120 degrees of Celcius / 248 degrees of Fahrenheit).

- Fastening to heat sink with a PU foam adhesive tape of automotive grade. Please find fastening details by clicking link: http://www.ledil.com/datasheets/DataSheet_TAPE.pdf


NOTE 1: We advise customer to ensure the suitability and sufficiency of the bond in the end product. For example, mechanical stress, vibration and holes on the surface of the circuit board weaken the strength of the tape.

NOTE 2: Assembly to the surface must be made straight, so the tape bonds constant and balanced with fastening surface. Slanted assembly might cause unbalanced bond to the surface. All surfaces where tape is applied must be clean, dry and free from grease and dirt.

If cleaning of PCB surfaces is needed, please follow strictly the cleaning instructions of your LED manufacturer - this is important as cleaning shall under no circumstances damage LEDs or other electronics components on the PCB.

Further note that optical components shall not be cleaned with any chemicals - only micro fiber cloth may be used to remove fingerprints or other traces from handling.

Relative intensity of FA11019_Tina-WW-WHT (XP-G)



D


C

B

A

4


4



Bottom view

3

3




Side view

9.7

Tape

2

2



Top view

Ø16.1

Note! Oval-version beam directions

MATERIALS
 Lens: PMMA
 Holder: PC
 Tape: PU Foam

This drawing is our property.
 It can't be reproduced
 or communicated without
 our written agreement.



L
T
F
F

e
e
i
i
N
n

d
h

DRAWING TITLE

Datasheet Assembly Tina-XP

1

1

DRAWN BY

DATE

p

9.8.2011

CHECKED BY

DATE

t

k

25.09.2008

SIZE

DRAWING NUMBER

REV

A4

2

DESIGNED BY

DATE

HH

22.07.2008

SCALE

2:1

WEIGHT (g)

-

SHEET

1/1

D

A