





Data Sheet


Illuminated Inspection Mirror and Magnetic Pick-up Set

	<p>Designed for viewing inaccessible and poorly lit areas Bright LED illumination Semi-rigid flexible shaft 350mm long Anodised handle with battery holder ON/OFF power switch in handle 3 sizes of viewing mirrors, 14, 23, and 30mm diameter 1 x Magnetic pick-up Power: 1 x AA battery (not supplied) Supplied in a fitted case</p> <table border="1" data-bbox="853 900 1500 974"> <tr> <td>RS Code</td> <td></td> </tr> <tr> <td>471-8806</td> <td></td> </tr> </table>	RS Code		471-8806	
RS Code					
471-8806					

	<p>Viewing Mirrors: Each mirror has a threaded shaft with a flat glass mirror mounted in a chrome plated housing 1 x 14mm diameter 1 x 23mm diameter 1 x 30mm diameter</p>
---	--

	<p>Magnetic pick-up Head Threaded chrome plated housing 12mm diameter magnet Recommended maximum load 250 grams</p>
---	--

	<p>Anodised Handle: 100mm long x 25mm diameter Holds 1 x AA battery Insert battery with + pole pointing towards lamp</p>
---	---

	<p>Illumination switch Switch situated at end of handle Rubber coated Positive click action On/Off Turn off lamp when not in use to conserve battery</p>
---	--