



Cartridge Heaters: Metric Low to High Watt Density

U.L. Recognized - E56973 C.S.A. Certified - LR-16386

Features

- Both Standard (MS) and Superwatt (MH) constructions are available.
- Wattages other than those listed are available.
- Made in U.S.A.

Diameter: 6.5 MM (6.38-6.48) Max Amp.MS-3.5, MH-4

Length/mm	Catalog No.	Min.Watts	Max Watts
40	MS6.5-40	10	50
50	MS6.5-50	10	65
60	MS6.5-60	10	75
60	MH6.5-60	90	*
70	MS6.5-70	10	90
70	MH6.5-70	105	*
80	MS6.5-80	10	110
80	MH6.5-80	130	*
90	MS6.5-90	10	125
90	MH6.5-90	145	*
100	MS6.5-100	10	145
100	MH6.5-100	165	*
110	MS6.5-110	10	160
110	MH6.5-110	185	*
120	MS6.5-120	10	170
120	MH6.5-120	205	*
130	MS6.5-130	10	185
130	MH6.5-130	225	*
140	MS6.5-140	10	200
140	MH6.5-140	240	*
150	MS6.5-150	10	215
150	MH6.5-150	260	*

Voltage

Standard voltages are either 120V or 240V. Other voltages are available.

Tolerances

Wattage tolerance is +5%, -10% at rated voltage.
 Diameter is always .001" less, but not more than .009" less, than the nominal (fractional) heater diameter.
 Length tolerances are ±2% with a ±1/16" minimum.