




All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to IEC 60169-15; EN 122110; MIL-STD-348A, Fig. 310

Documents

N/A

Material and plating

Connector parts

Center contact
Outer contact
Dielectric
Gasket
Coupling nut

Material

Brass
Stainless steel
PTFE
Silicone
CuBe or equivalent

Plating

AuroDur®, gold plated
Gold, 0.1 µm min.

Gold, 0.1 µm

**ADAPTOR
SMA PLUG – PLUG**
32S103-S00L5
Electrical data

Impedance	50 Ω
Frequency	DC to 18 GHz
VSWR	$\leq 1.05 + 0.005 \times f \text{ [GHz]}$
Insertion loss	$\leq 0.03 \times \sqrt{f \text{ (GHz)}} \text{ dB}$
Insulation resistance	$\geq 5 \times 10^3 \text{ M}\Omega$
Center contact resistance	$\leq 3 \text{ m}\Omega$
Outer contact resistance	$\leq 2 \text{ m}\Omega$
Test voltage	1000 V rms
Working voltage	480 V rms
Power handling (at 20 °C, sea level, VSWR 1.0)	$\leq 200 \text{ W @ 2 GHz}$
RF-leakage	$\geq 100 \text{ dB up to 1 GHz}$

Mechanical data

Mating cycles	min. 500
Coupling nut retention	$\geq 270 \text{ N}$
Center contact captivation: axial	$\geq 27 \text{ N}$
radial	$\geq 3 \text{ Ncm}$
Coupling test torque	max. 1.7 Nm
Recommended torque	0.8 Nm to 1.1 Nm

Environmental data

Temperature range	-65°C to +165°C
Thermal shock	MIL-STD-202, Meth. 107, Cond. B
Corrosion	MIL-STD-202, Meth. 101, Cond. B
Vibration	MIL-STD-202, Meth. 204, Cond. D
Shock	MIL-STD-202, Meth. 213, Cond. I
Moisture resistance	MIL-STD-202, Meth. 106
2002/95/EC (RoHS)	compliant

Tooling

N/A

Suitable cables

N/A

Packing

Standard	1 pce in bag
Weight	5.86 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Rong Fang	30/03/04	A. König	18/09/07	c00	07-0650	S. Huber-Siegl	18/09/07

Rosenberger Hochfrequenztechnik GmbH & Co. KG
P.O.Box 1260 D-84526 Tittmoning Germany
www.rosenberger.de

Tel.: +49 8684 18-0
Fax: +49 8684 18-499
email: info@rosenberger.de

Page
2 / 2