

79 02 120

Precision Electronics Diagonal Cutter





- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Very precisely ground and sharp cutting edges with very small bevels for exact cutting on delicate electronic components; also available without bevel for flush cutting
- Cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint with carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Ball bearing chrome steel, forged, multi stage oil-hardened
- Mini-head

The subtle difference

KNIPEX precision electronics pliers are made of high-quality ball bearing steel and processed with the highest degree of care. Each opening movement is gentle and even without backlash. Each work step proceeds reliably and precisely. This makes work much easier for professionals.

Article No.	79 02 120
EAN	4003773061281
Pliers	burnished
Head	polished
Handles	with multi-component grips
Style	0
Cutting capacities medium hard wire (diameter) Ø mm	1,0
Cutting capacities hard wire (diameter) Ø mm	0,6
Cutting capacities soft wire (diameter) Ø mm	0,2 - 1,4
B mm	6,5
D mm	6,5
A mm	9
Nominal size	120 mm
Length mm	120
Net weight g	57



technical change and errors excepted

