


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
H	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A		INITIAL RELEASE	24NOV2009	RC	AH



LC CONN. MARK	LC CONN. MARK
A	B
B	A

NOTES:

- 1 ATTENUATION ≤ 0.3 dB, MEASURED AT 850 nm OR 1300 nm ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
 - 2 RETURN LOSS ≥ 20 dB, IN MATED CONDITION AGAINST REFERENCE CONNECTOR AT 850 nm OR 1300 nm
 - 3 TEST RESULT SHEET IS SUPPLIED WITH EACH INDIVIDUAL PACKED ASSEMBLY
 - 4 CABLE INFORMATION:
 - CORE DIAMETER: 62.5/125 μ m
 - OUTER JACKET DIAMETER: 1.8x3.6 mm
 - OUTER JACKET COLOUR: GREY
 - OUTER JACKET MATERIAL: LSZH
- BLANK LABEL

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-2061309-Y	XY.0

2	BLANK LABEL	3
2	LC DUPLEX CONNECTOR, MULTI MODE, BEIGE	2
L	FOCAB 1.8MZ 62.5/125, GREY, LSZH	1
Qty	Description	Item
THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm -$ 1 PLC $\pm -$ 2 PLC $\pm -$ 3 PLC $\pm -$ 4 PLC $\pm -$ ANGLES $\pm -$ FINISH -
MATERIAL -		DWN R. COOLEN 16OCT2009 CHK A. HENGELMOLEN 16OCT2009 APVD A. HENGELMOLEN 16OCT2009 PRODUCT SPEC - APPLICATION SPEC - WEIGHT - CUSTOMER DRAWING
Tyco Electronics Tyco Electronics Corporation 's-Hertogenbosch, Nederland		NAME FIBER OPTIC LEAD 1.8MZ LC/DPX - LC/DPX MULTI MODE 62.5/125
SIZE A2	CAGE CODE 00779	DRAWING NO. C=2061309
SCALE NTS		SHEET 1 OF 1
REV A		RESTRICTED TO -

2061309