


Capacitor, Tantalum, SMD, Polymer, Molded, Low ESR, AEC-Q200, 33 uF, 3528, +/-20% Tol, 6.3 VDC (105C)



General Information	
Supplier:	KEMET
Brand:	Kemet
Application:	Automotive/Low ESR (AEC-Q200 Qualified)
Sub Application:	(NonCombustibleCathode)
Part Type Description:	SMD, Polymer, Molded, Low ESR, AEC-Q200
Construction:	Standard Chip-Polymer
Body Type:	Molded Chip
Footprint:	3528
Weight:	94.85 mg
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	3.5	+/-0.2
W	2.8	+/-0.2
H	1.9	+/-0.1
F	2.2	+/-0.1
S	0.8	+/-0.3
B	0.4	+/-0.15
X	0.1	+/-0.1
P	0.5	REF
R	1	REF
T	0.13	REF
A	1.1	MIN

Specifications	
Capacitance:	33 uF
Tolerance:	+/-20%
Voltage:	6.3 VDC (105C)
Voltage:	4.22 VDC (125C)
Temperature Range:	-55/+125C
Testing:	AEC-Q200
Current/Ripple Current:	1260 mA (25C)
Current/Ripple Current:	1134 mA (85C)
Current/Ripple Current:	315 mA (125C)
Resistance/ESR:	80 mOhms (100kHz)
Failure Rate:	NA
Leakage Current:	20.8 uA
Dissipation Factor:	8%

Packaging Specifications	
Package Kind:	T&R
Package Size:	7in
Package Quantity:	2000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.