


2415
Max. 65 W
Programmable chargers for NiMH/NiCd batteries

- Universal inngangsspenning
- Medisinsk godkjent (EN 60601)
- UL godkjenning påventes
- CPM-Computer Programmerbar Microprocessor tilbyr:
 - Ladedeteksjonsvalg (en eller fler):
 - dV, dT/dt, 0 dV, Timer
 - Justering av sikkerhetstimer, dV nivå og temp. stigningsnivå
- Tilpasninger leveres på forespørsel
- Utskiftbare DC plugger
- Universal input voltage
- Medical approved (EN 60601)
- UL approval pending
- CPM-Computer Programmable Microprocessor offering:
 - Charge detection options (one or more):
 - dV, dT/dt, 0 dV, Timer
 - Safety timer, dV threshold, and Temperature gradient adjustment
- Custom specifications on request
- Exchangeable DC plugs



Tekniske data	Technical specifications	
Inngangsspenning	Input voltage	90-264 VAC, 50-60Hz
Maks. utgangseffekt	Max. Output power	65W
Strømtrekk fra batt v. frakoblet nett	Leakage current f. battery w mains off	< 1mA
Start timer (ingen -dV deteksjon) **	Start timer (no -dV detection) **	3 min.
Top-off timer **	Top-off timer **	1 time/hour
Sikkerhetstimer **	Safety timer **	2 timer/hours
Svitsjefrekvens	Switch frequency	40 kHz
Temperaturområde	Temperature range	-20 - +40 °C
Virkningsgrad (ved 100% last)	Efficiency (at 100% load)	ca 78 %
Sikring	Protection	
* Inngang	* Input	Sikring/Fuse
* Utgang	* Output	Polyswitch-sikring mot polvendning/ Polyswitch fuse against reversed polarity
Isolasjonsklasse	Insulation class	II
Elektrisk sikkerhet	Electrical safety	EN 60601-1, EN 60950, EN 60335-2-29
EMC standarder	EMC standards	
* Medisinsk	* Medical	EN 60601-1-2
* Emisjon	* Emission	EN 61000-6-3
* Immunitet	* Immunity	EN 61000-6-1
Nettilkopling	Mains connection	2 pins IEC 320
IP grad	IP code	41
Mål (LxBxH)	Dimensions (LxWxH)	135 x 80 x 44mm
Vekt	Weight	350g
** Annet	** Other	Laderen er programmerbar – se data The charger is programmable – see spec for Mascot CPM

* Nettledning følger ikke med. Må bestilles i tillegg. *Mains cable not included. Order separately.*

Versjoner – versions

Celler	Tomgangs-spenning	Min utsp. for -dV deteksjon	Max utsp. for -dV deteksjon	-dV deteksjon mV/celle eller %	Hurtig lade strøm	Topplading (lt. e. -dV detek.)	Vedlikeholds-lade strøm (mA)
Cells	No-load voltage	Min. out. for -dV detection	Max out. for -dV detection	-dV detection mV/cell or %	Fast charge current	Top-off charge (lh. a. -dV det.)	Trickle charge current (mA)
3-6	12,8V +/-0,7V	3,7V (min. 3 c.)	10,8V (max 6 c.)	11mV/0,6%	4,5A +/- 350mA	630mA +/- 100mA	150 +/- 50
4-8	16,5V +/-1V	5,0V (min. 4 c.)	14,4V (max 8 c.)	8mV/0,5%	4,0A +/- 300mA	560mA +/- 80mA	130 +/- 50
5-10	21V +/-1,2V	6,2V (min. 5 c.)	18V (max 10 c.)		3,5A +/- 300mA	480mA +/- 70mA	100 +/- 50
6-12	24,7V +/-1,5V	7,5V (min. 6 c.)	21,6V (max 12 c.)		3,0A +/- 200mA	420mA +/- 60mA	100 +/- 50
10-20	41V +/-2V	12,5V (min. 10 c.)	36V (max 20 c.)		1,8A +/- 100mA	250mA +/- 50mA	60 +/- 30
12-25	51V +/-2V	15V (min. 12 c.)	45V (max 25 c.)		1,5A +/- 100mA	210mA +/- 50mA	50 +/- 30
Note:		min 1,25 V pr. cell	max 1,8 V pr. cell				

23052006

www.mascot.no
sales@mascot.no
Phone:
Fax:

Main Office
PO Box 177
N-1601 FREDRIKSTAD
NORWAY
+47 69 36 43 00
+47 69 36 43 01

Mascot UK
Box 2090, Salisbury
Wiltshire SP2 2BH
UK
+44 1722 504 853
+44 845 299 1210

Mascot DE-AT-CH-BENELUX
Hirschbergstr. 28/7
D-74838 LIMBACH
GERMANY
+49 6287 95140
+49 6287 95141

Tettanger Str. 52
D-88239 WANGEN
GERMANY
+49 7528 95 16 77
+49 7528 95 16 78

Mascot France
38 rue Leo Lagrange
94270 Le Kremlin Bicêtre
FRANCE
+33 1 46 58 71 85
+33 1 46 58 71 85

Programmable chargers for NiMH/NiCd batteries

Programmerbare ladere for NiMH/NiCd batterier

Rechargeable NiMH batteries

are rapidly becoming more advanced and their uses are spreading into a wide variety of applications. Accordingly, the demands on the battery chargers have increased. For safe and fast battery charge, new chargers must be able to handle a broad range of battery specifications. Mascot has seen this development and introduces a new range of intelligent models from 16W to 65W to meet the demand for more flexible and versatile battery chargers.

The standard models are fast chargers using -dV detection, but the chargers are equipped with a Computer Programmable Microprocessor (CPM), so they can readily be programmed to fit a variety of specifications. These charge detections include (one or more options combined):

- -dV
- dT/dt
- 0 dV
- Timer only

In addition, adjustments can be made to:

- safety timer
- -dV threshold
- temperature gradient

All models are equally well suited for charging NiCd batteries. Other key features include: automatic polyswitch fuse against reversed polarity on output. Compliance with international standards for medical use (EN 60601). Custom and waterproof units (IP 67) are available on request.

Oppladbare NiMH batterier

er i dag både svært populære og avanserte, og de har spredt seg til mange forskjellige bruksområder. Dette stiller høyere krav til laderne, som skal kunne håndtere mange ulike NiMH batterityper og samtidig sikre full opplading, både raskt og sikkert. Mascot har sett denne utviklingen og introduserer nå en ny serie med intelligente batteriladere som ivaretar krav til både ladefleksibilitet og sikkerhet.

Standardmodellene er hurtigladdere med -dV ladekontroll, men alle laderne er utstyrt med en Computer Programmerbar Mikroprosessor (CPM), slik at de

kan raskt omprogrammeres til andre ladekontrollfunksjoner. Disse ladefunksjonene er (en eller flere parametre kombinert):

- -dV
- dT/dt
- 0 dV
- Kun timer

I tillegg kan følgende parametre justeres:

- sikkerhetstimer
- -dV nivå
- temperaturgradient

Samtlige modeller er også velegnet for lading av NiCd batterier. Laderne har automatisk polyswitch-sikring mot polvendning på utgang, og er godkjente for medisinsk bruk i hht EN 60601. Spesialtilpasninger og vanntette (IP67) enheter leveres på forespørsel.

