


## MCVR 1,5/ 5-ST-3,5

Order No.: 1863181

The figure shows a 10-position version of the product



Plug component, nominal current: 8 A, rated voltage: 160 V, pitch: 3.5 mm, no. of positions: 5, type of connection: Screw connection

### Commercial data

|                          |                    |
|--------------------------|--------------------|
| EAN                      | 4017918120993      |
| Pack                     | 50 Pcs.            |
| Customs tariff           | 85366990           |
| Weight/Piece             | 0.0042 KG          |
| Catalog page information | Page 128 (CC-2007) |

### Product notes

WEEE/RoHS-compliant since:  
01/01/2003



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

### Technical data

#### Dimensions / positions

|                     |         |
|---------------------|---------|
| Height              | 12.5 mm |
| Pitch               | 3.5 mm  |
| Dimension a         | 14 mm   |
| Number of positions | 5       |
| Screw thread        | M 2     |

|                                    |  |
|------------------------------------|--|
| Tightening torque, min             | 0.22 Nm  |
| <b>Technical data</b>              |  |
| Insulating material group          | I  |
| Rated surge voltage (III/3)        | 2.5 kV   |
| Rated surge voltage (III/2)        | 2.5 kV   |
| Rated surge voltage (II/2)         | 2.5 kV   |
| Rated voltage (III/2)              | 160 V  |
| Rated voltage (II/2)               | 320 V  |
| Connection in acc. with standard   | EN-VDE   |
| Nominal current $I_N$              | 8 A  |
| Nominal voltage $U_N$              | 160 V  |
| Nominal cross section              | 1.5 mm <sup>2</sup>                                    |
| Maximum load current               | 8 A (with 1.5 mm <sup>2</sup> conductor cross section) |
| Insulating material                | PA   |
| Inflammability class acc. to UL 94 | V0   |
| Internal cylindrical gage          | A1   |
| Stripping length                   | 7 mm   |

|  |                      |
|--|----------------------|
| <b>Connection data</b>   |                      |
| Conductor cross section solid min.   | 0.14 mm <sup>2</sup> |
| Conductor cross section solid max.   | 1.5 mm <sup>2</sup>  |
| Conductor cross section stranded min.                                      | 0.14 mm <sup>2</sup> |
| Conductor cross section stranded max.                                      | 1.5 mm <sup>2</sup>  |
| Conductor cross section stranded, with ferrule without plastic sleeve min. | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule without plastic sleeve max. | 1.5 mm <sup>2</sup>  |
| Conductor cross section stranded, with ferrule with plastic sleeve min.    | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule with plastic sleeve max.    | 0.5 mm <sup>2</sup>  |
| Conductor cross section AWG/kcmil min.                                     | 28                   |
| Conductor cross section AWG/kcmil max                                      | 16                   |
| 2 conductors with same cross section, solid min.                           | 0.08 mm <sup>2</sup> |
| 2 conductors with same cross section, solid max.                           | 0.5 mm <sup>2</sup>  |

|   |                      |
|---|----------------------|
| 2 conductors with same cross section, stranded min.                                     | 0.08 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded max.                                     | 0.75 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.   | 0.25 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.   | 0.34 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min. | 0.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max. | 0.5 mm <sup>2</sup>  |

### Certificates / Approvals

#### Approval logo



#### CUL

|                                |       |
|--------------------------------|-------|
| Nominal voltage U <sub>N</sub> | 300 V |
| Nominal current I <sub>N</sub> | 8 A   |
| AWG/kcmil                      | 30-14 |

#### UL

|                                |                            |
|--------------------------------|----------------------------|
| Nominal voltage U <sub>N</sub> | 300 V                      |
| Nominal current I <sub>N</sub> | 8 A                        |
| AWG/kcmil                      | 30-14                      |
| Certification                  | CB, CUL, GOST, UL, VDE-PZI |

### Accessories

| Item | Designation | Description |
|------|-------------|-------------|
|------|-------------|-------------|

#### Marking

|         |                         |  |
|---------|-------------------------|--|
| 1051993 | B-STIFT                 | Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm  |
| 0804073 | SK 3,5/2,8:FORTL.ZAHLEN | Marker card, printed horizontally, self-adhesive, 10-section marker strip, 14 identical decades marked 1-10, 11-20 etc. up to 91-100, sufficient for 140 terminal blocks |

|         |                        |   |
|---------|------------------------|---|
| 0805030 | SK 3,5/2,8:SO          | Marker card, special printing, self-adhesive, labeled acc. to customer requirements, 14 identical marker strips per card, max. 25-position labeling per strip, color: White               |
| 0803883 | SK U/2,8 WH:UNBEDRUCKT | Unprinted marker cards, DIN A4 format, pitch as desired, self-adhesive, with 50 stamped marker strips, 185 mm strip length, can be labeled with the CMS system or manually with the M-PEN |

### Tools

|         |             |  |
|---------|-------------|--|
| 1205037 | SZS 0,4X2,5 | Screwdriver, bladed, matches all screw terminal blocks up to 1.5 mm <sup>2</sup> connection cross section, blade: 0.4 x 2.5 mm |
|---------|-------------|--|

### Additional products

| Item           | Designation       | Description   |
|----------------|-------------------|---|
| <b>General</b> |                   |   |
| 1897128        | EMC 1,5/ 5-G-3,5  | Header, nominal current: 8 A, rated voltage: 160 V, pitch: 3.5 mm, no. of positions: 5, mounting: press in  |
| 1911046        | EMCV 1,5/ 5-G-3,5 | Header, nominal current: 8 A, rated voltage: 160 V, pitch: 3.5 mm, no. of positions: 5, mounting: press in  |
| 1844249        | MC 1,5/ 5-G-3,5   | Header, nominal current: 8 A, rated voltage: 160 V, pitch: 3.5 mm, no. of positions: 5, mounting: Soldering |
| 1843635        | MCV 1,5/ 5-G-3,5  | Header, nominal current: 8 A, rated voltage: 160 V, pitch: 3.5 mm, no. of positions: 5, mounting: Soldering |

### Drawings

#### Diagram



---

Dimensioned drawing

---

