



LOC		DIST		REVISIONS					
AD		00		REV	LYR	DESCRIPTION	DATE	DWN	APVD
				C		REV PER ECO-11-007577	13APR2011	RKC	JE


- 1
- PCB HOLE DIM:
DRILLED HOLE = 0.700±0.025mm
FINISHED HOLE = 0.600±0.050mm
Cu THICKNESS = 0.0375±0.0125mm
SnPb THICKNESS = 0.007±0.003mm
- 2
- MATERIAL:
CONTACT & SHIELD - PHOSPHOR BRONZE
HOUSING & CHICKLET - GLASS FILLED POLYESTER
- 3
- FINISH: SIGNAL AND GROUND CONTACTS:
MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF
PRODUCT SPECIFICATION 108-2055; BASED ON TELCORDIA
GR-1217-CORE, APPLICATIONS IN UNCONTROLLED
ENVIRONMENTS
COMPLIANT PIN AREA: 0.5µm MIN BRIGHT
TIN-LEAD OVER BASE PLATING
- 4
- CONNECTOR MARKED WITH PART NUMBER AND
DATE CODE IN APPROXIMATE AREA SHOWN
- 5
- DIMENSION APPLIES TO CENTERLINE OF THRU HOLE
- 6
- DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
7. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT.
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995



RECOMMENDED PC BOARD LAYOUT
COMPONENT SIDE SHOWN
SCALE: 4:1



TOP SURFACE OF
DAUGHTER CARD



1469169-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. J. MAGARO 02DEC2003	TE Connectivity	
DIMENSIONS:		CHK D. S. SZCZESNY 02DEC2003		
mm		APVD R. PATTERSON 31MAR2006	NAME HEADER ASSEMBLY, RIGHT ANGLE, 2 PAIR, COPLANAR, HMZd	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	SIZE A100779	
9 PLC ±		APPLICATION SPEC	CAGE CODE C=1469169	
3 PLC ±		WEIGHT	RESTRICTED TO	
5 PLC ±		CUSTOMER DRAWING	SCALE 6:1	
4 PLC ±			SHEET 1 OF 1	
ANGLES ±			REV C	
FINISH				